

10048700	<b>DATA SHEET</b>	
Valid from: 22.06.2022	<b>EPIC® H-B 10 KDBF</b>	

## Beschreibung

- Protective plastic cover for housings H-B 10 / 16 / 24
- Suitable for panel mounted housings, surface mounted housings, coupler hoods



## General Characteristics

Series	See table
Version	KDBF
Locking	Bolts for single lever
Loss protection	Cord
Protection (DIN EN 60529)	IP 65 (latched)
Temperature Range	-25°C to +50°C

## Materials / Surfaces

Cover	Polyamid (UL 94/V0), grey
-------	---------------------------

## Versions

Article number	Article description	Series
10048700	EPIC® H-B 10 KDBF	H-B 10
10088700	EPIC® H-B 16 KDBF	H-B 16
10118700	EPIC® H-B 24 KDBF	H-B 24

## Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP Released: IVSE1/PDP	Document: DB10048700EN Version: 03	Page 1 of 1
---	---------------------------------------	-------------