Valid from: PIC® SIGNAL M23 A3 N

& LAPP

28.03.2019

Description

- · Circular connectors for servo cables and encoders
- Housings are very flexible cable connectors with wide clamping range, receptacle housings for assembling the inserts from the front and rear
- Permanent vibration protection



General characteristics

Series SIGNAL M23

Version panel-mount connector, angled, rotatable, front wall mounting

Protection rating IP 65

Temperature range -25°C to +125°C

Product variations

Article number	Coding	Fastening type	PU
24420055	black (N)	Ø2,7mm (4x)	5
24420054	black (N)	Ø2,7mm (4x)	20

Materials and surfaces

Housing Blue chromated (CrVI free), zinc die-casting

Sealing FPM/FKM

Approvals

UL File Number E249137





Standard


Safety Standard IEC 61984; UL 1977; UL 2238; CSA 22.2 182.3

24420055	DATA SHEET	
Valid from: 28.03.2019	EPIC [®] SIGNAL M23 A3 N	

Drawings









Good chemical resistance



Industrial machinery and plant engineering



Robust



Waterproof



Wind energy

Info

Rotateable with clearly defined adjustment positions

Application range

Plant engineering Servo drives and Servo assemblies Measurement and control technology

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: STKU3/PDP	Document: DB24420055EN	Dage 2 of 2
Released: IVSE1/PDP	Version: 04	Page 2 of 2