44423200

DATA SHEET

Valid from: 17.09.2018

EPIC® H-BE 6 SP / H-BE 6 BP



Description

Standard inserts with Push-In connection
 The EPIC® H-BE series is suitable for applications that require a reliable connection when working with high voltages and currents





General Characteristics

Series H-BE 6

Version Male/Female (Article 44423201)

Conductor conductor stiff or flexible with cable end-sleeves

Number of Contacts 6 + PE

Connection Push-In: 0,14-2,5 mm²

Temperature Range -40°C to +100°C, short-term up to +125°C

Mechanical Characteristics

Cycle of mechanical operation 500

Electrical Characteristics

Rated Voltage, IEC 500 V
Rated Impulse Voltage 6 kV
Rated Current, IEC 16 A

Contact Resistance < 3 mOhm

Degree of Soiling 3

Materials and Surfaces

Contacts Copper alloy, hard silver-plated

Insulating Body PA Flammability Class according to UL 94 V0

Approvals

none


Standard

Safety Standard IEC 61984


DATA SHEET





Technical Drawings




Male part, dimensions









Female part, dimensions











Temperature resistant

Info

Multifunctional insert for versatile appliactions Screw, crimp, cage clamp and Push-In version - freely combinable

Application range

Mechanical engineering Light & sound technology Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

| Creator: JOKR1/PDP | Document: DB44423200EN | Page 2 of 2 |
|---------------------|------------------------|-------------|
| Released: IVSE1/PDP | Version: 01 | |