


2170016	DATA SHEET	
valid from: 29.04.2019	RG-6 A/U	

Application

RG-6 A/U are coaxial cables for radio and computer systems, as well as applications related to commercial radio-frequency (high frequency) technology and electronics.

They allow distortion-free and low-attenuation transmission of signals with a high bandwidth over shorter distances.

The cable is intended for limited movements and for fixed installation in dry and damp interiors and outdoors. It meets the requirements concerning high ambient temperatures and chemical stress.

Design

Design	Cable design and electrical properties of M17/2-RG6 to MIL-C-17. Designation in accordance with MIL-DTL-17 H: M17/180-00001
Conductor	Inner conductor: Solid bare copper clad steel wire Ø: 0.724 ± 0.025 mm
Insulation	PE, 4.7 mm Ø
Screen	Outer conductor: braid of bare copper wires coverage 95 % (nominal value)
Outer sheath	PVC, black Outer diameter: 8.43 ± 0.1 mm

Electrical properties at 20°C

Conductor resistance	Inner conductor: max. 144 Ω/km
Insulation resistance	min. 5 GΩ x km
Mutual capacitance	max. 67 pF/m (1 kHz)
Characteristic impedance	75 ± 3 Ω
Attenuation	max. 14 dB/100 m (200 MHz) max. 20 dB/100 m (400 MHz)
Velocity of propagation	66 %
Rated voltage	2 kV (50 Hz)
Test voltage	5 kV

Mechanical and thermal properties

Minimum bending radius	occasional flexing: 10 x cable Ø fixed installation: 6 x cable Ø
Temperature range	fixed installation: -40 °C up to 80 °C
Flammability	flame retardant acc. to IEC 60332-1-2
General requirements	This cable is conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances).

Creator: PESA / PDC	Document: DB2170016EN	Page 1 of 1
Released: ALTE / PDC	Version: 03	