

Valid from: 23.06.2022

EPIC[®] H-B 10 KDBF

Beschreibung

- Protective plastic cover for housings H-B 10 / 16 / 24
- Suitable for panel mounted housings, surface mounted housings, coupler hoods



General Characteristics

Series	See table
Version	KDBF
Locking	Bolts for single lever
Loss protection	Cord
Protection (DIN EN 60529)	IP 65 (latched)
Temperature Range	-25°C to +50°C

Materials / Surfaces

Cover

Polyamid (UL 94/V0), grey

Versions

Article number	Article description	Series
10048700	EPIC® H-B 10 KDBF	H-B 10
10088700	EPIC® H-B 16 KDBF	H-B 16
10118700	EPIC® H-B 24 KDBF	H-B 24

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP	Document: DB10048700EN	Page 1 of 1		
Released: IVSE1/PDP	Version: 03			
We recerve all rights according to DIN ISO 16016				