10152000	DATA SHEET
Valid from:	EPIC [®] H-B 48 AD



Description

01.04.2022

- The large, robust housing for two inserts in one connector
- Power and data in one connector



General Characteristics

Series H-B 48

Version Panel mount base with cover

Locking Single lever

Protection (DIN EN 60529) IP 65 (latched with hood)

Temperature Range -40°C to +100°C, short term up to +125°C

Materials / Surfaces

Housing Aluminium alloy, powder-coated, grey

Locking Steel, zinc-plated

Sealing NBR Cover PA

Standard


Safety Standard IEC 61984

Versions

Article number	Article description
10152000	EPIC® H-B 48 AD

10152000	DATA SHEET	MIADD
Valid from: 01.04.2022	EPIC [®] H-B 48 AD	WLAPP

Technical Drawings





Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Application range

Plant engineering, Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.