10390413

DATA SHEET

Valid from: 17.09.2018

EPIC® MCB BUS PIN 1x(4) CM



Description

- Shielded modul for data and signal transmission
- Crimp connection for permanent vibration proof contact
- CAT5e up to 1 Gigabit/s
- Cable clamp 3-9mm
- The mix of different functions in one plug guarantees high flexibilty



General characteristics

Contact type socket

Number of contacts 4 + shield

Mating cycles 500

Material PA

Pollution degree 3

Temperatue range -40° C to +125° C


Termination methods crimp termination: 0.14 – 2,5 mm


Electrical characteristics

Rated voltage 50 V
Rated impuls voltage 0,8 kV
Rated current 10 A

Drawings







Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB10390413EN	Page 1 of 1
Released: IVSE1/PDP	Version: 01	