19035900	DATA SHEET	Φ I A DI
Valid from: 17.09.2018	EPIC [®] H-B 10 SGRL-LB	WLAPI

Description

- The smallest housing with single and double lever.
- The right housing is available for every application.



General Characteristics

Series H-B 10

Version Hood M20 / M25 (Article 79061600)

Locking Single lever

Cable entry 2

Protection (DIN EN 60529) IP 65 (latched)
Protection (NEMA 250, UL50E) 12 (latched)

Temperature Range -40°C to +100°C, short term up to +125°C

Materials and Surfaces

Housing Aluminium alloy, powder-coated, grey
Bolt Heat-treatable steel, zinc-plated

Lever Steel, zinc-plated

Profile Seal NBR

Approvals

VDE-Approval, VDE-REG.-Nr. B437

Standard


Safety Standard IEC 61984

19035900	DATA SHEET
Valid from: 17.09.2018	EPIC [®] H-B 10 SGRL-LB



Technical Drawings









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 10

Application range

Plant engineering Light & sound technology Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB19035900EN	Daga 2 of 2
Released: IVSE1/PDP	Version: 01	Page 2 of 2