Valid from: 17.09.2018

EPIC<sup>®</sup> H-B 10 TBF



### Description

- The smallest housing with single and double lever.
- The right housing is available for every application.



#### **General Characteristics**

Series	H-B 10
Version	Cable coupler hood M20 / M25 (Article 79040200)
Cable gland	No
Locking	Double lever
Cable entry	Straight
Protection (DIN EN 60529)	IP 65 (latched)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C
Materials and Surfaces	

Housing	Aluminium alloy, powder-coated, grey
Bolt	Heat-treatable steel, zinc-plated
Lever	Steel, zinc-plated
Profile Seal	NBR

# Approvals

VDE-Approval, VDE-REG.-Nr.

#### Standard

Safety Standard

B437

IEC 61984


	Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB19046000EN Version: 01	Page 1 of 2	
	Released. IV CE I/ I BI			
We reserve all rights according to DIN ISO 16016				

Valid from: 17.09.2018



## **Technical Drawings**









Automation



Industrial machinery and plant engineering





Mechanical resistance



Robust

Waterproof

Info Universal, robust metal housings size H-B 10

#### **Application range**

Plant engineering Light & sound technology **Plastics industry** 

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB19046000EN	Page 2 of 2		
Released: IVSE1/PDP	Version: 01			
We reserve all rights according to DIN ISO 16016.				