19512702 DATA SHEET

Valid from: 09.08.2018 EPIC® ULTRA H-A 3 AGSV M20



Description

- EMC protection
- Corrosion-resistant
- Protection rating UL50E tested
- All-purpose due to high corrosion resistance and high environmental protection



General Characteristics

Series ULTRA H-A 3

Version Surface-mount base M20

Locking mechanism

Cable entry

Straight

Thread

M20x1.5

Protection (DIN EN 60529)

Protection (MEMA 650 HM 505)

Protection (NEMA 250, UL50E) 4, 4X, 12 (latched)

Temperature range -40°C to +100°C, short-term up to +125°C

Holding screws for inserts included Yes
Cable Gland included No

Materials and Surfaces

Housing, base material Zinc die-casting
Housing, surface Nickel-plated
Lever Stainless steel
Holding screws for inserts Stainless steel

Gasket

Approvals

VDE-Approval, VDE-REG.-Nr. B437 UL-Approval UL-E-File Number E75770

Standards

Safety Standard IEC 61984; UL 1977


Creator: BEGE1/PDP	Document: DB19512702EN	Page 1 of 2
Released: IVSE1/PDP	Version: 00	


19512702	DATA SHEET	
Valid from:	EPIC [®] ULTRA H-A 3 AGSV M20	



Technical Drawing

09.08.2018





Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP	Document: DB19512702EN	Page 2 of 2
Released: IVSE1/PDP	Version: 00	