Valid from: EPIC® H-B 24 TG 2X



Description

17.09.2018

 Ideal for many applications due to a wide range of housings and inserts



General Characteristics

Series H-B 24

Version Hood 2X M25 / 2XM32 (Article 44422020)

Locking Bolts for double lever

Gland body Yes
Cable entry 2 Straight
Protection (DIN EN 60529) IP 65 (latched)
Protection (NEMA 250, UL50E) 12 (latched)

Temperature Range -40°C to +100°C, short term up to +125°C

Materials and Surfaces

Housing Aluminium alloy, powder-coated, grey
Bolt Heat-treatable steel, zinc-plated

Gland body Brass, nickel plated

Approvals

VDE-Approval, VDE-REG.-Nr. B437

Standard

Safety Standard IEC 61984


DATA SHEET 44422019 Valid from: EPIC® H-B 24 TG 2X




Technical Drawings

17.09.2018











Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 24

Application range

Plant engineering Light & sound technology Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB44422019EN	Page 2 of 2
Released: IVSE1/PDP	Version: 01	