DATA SHEET 44423365 Valid from:

EPIC® MHB 2 40A CM



Description

26.04.2022

Power module 2-pin for compact power transmission

Crimp connection for permanent vibration-proof

EPIC® MH system is mateable with the market standard

The mix of different functions is one plug guarantees high flexibility



General characteristics

Contact type socket Number of contacts 2 Mating cycles 500

Material Polyamide, glass fibre-reinforced

Inflammability class acc. with UL 94 V0 Pollution degree

Temperatue range -40° C to +125° C

Termination methods crimp termination: 1.5 - 10 mm²

> Epic® MH 6 multi-frame Epic® MH 10 multi-frame Epic® MH 16 multi-frame

Epic® MH 24 multi-frame

Epic® MH 4.0mm contacts Suitable contacts

Electrical characteristics

Suitable frame

1000 V (Conductor-PE); 1000 V (Conductor-Conductor) Rated voltage

< 5 mΩ Contact resistance 8 kV Rated impuls voltage Rated current 40 A

Standards/Approvals


cURus according to UL 1977: in preparation


according EN 45545-2 Fire protection on railway vehicles


> requirement sets R22 and R23 hazard level HL1, HL2 and HL3

44423365	DATA SHEET	& LADD
Valid from: 26.04.2022	EPIC® MHB 2 40A CM	WLAPP

Drawings







Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: JOKR1/PDP	Document: : DB44423365EN	Do 70 2 of 2
Released: IVSE1/PDP	Version: 00	Page 2 of 2