70045200	DATA SHEET
Valid from:	EPIC <sup>®</sup> H-B 10 SDRH-BO



# Description

17.09.2018

- The smallest housing with single and double lever.
- The right housing is available for every application.



#### **General Characteristics**

Series H-B 10

Version Surface mount base PG21 / PG29 (Article 70045400)

Protection cover Yes

Locking Bolts for double lever

Cable entry

Protection (DIN EN 60529)

IP 65 (latched)
IP 40 (cover closed)

Protection (NEMA 250, UL50E) 4, 12 (latched)

Temperature Range -40°C to +100°C, short term up to +125°C

### **Materials and Surfaces**

Housing Aluminium alloy,powder-coated, grey
Cover Zinc alloy, powder-coated, grey

Bolt Zinc plated steel

Profile Seal NBR

#### **Approvals**

VDE-Approval, VDE-REG.-Nr. B437

#### **Standard**

Safety Standard IEC 61984


## **DATA SHEET** 70045200 Valid from: EPIC® H-B 10 SDRH-BO



# **Technical Drawings**

17.09.2018









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

### Info

Universal, robust metal housings size H-B 10

# **Application range**

Plant engineering Light & sound technology Plastics industry

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB70045200EN	D0
Released: IVSE1/PDP	Version: 02	Page 2 of 2