70444000	DATA SHEET	Ø I ADD
Valid from: 17.09.2018	EPIC [®] H-A 10 AD-LB	WLAPP

Description

- These connectors are attractive because of their compact housing.
- Small and space-saving for narrow available space



General characteristics

Series H-A 10

Version Panel-mount base Locking single lever

Protection cover yes

Protection (DIN EN 60529) IP 65 (latched)
Protection (NEMA 250, UL50E) 4, 12 (latched)

Temperature range -40°C to +100°C, short-term up to +125°C

Materials and surfaces

Housing Aluminium alloy, powder-coated, grey Protection cover Zinc alloy powder-coated, grey

Lever Steel, zinc-plated

Gasket NBR

Approvals

VDE-Approval, VDE-REG.-Nr. B437


Standards

Safety Standard IEC 61984

70444000	DATA SHEET	& LADD
Valid from: 17.09.2018	EPIC [®] H-A 10 AD-LB	WLAPP

Drawings









Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Compact, robust metal housings size H-A 10

Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB70444000EN	Dago 2 of 2
Released: IVSE1/PDP	Version: 01	Page 2 of 2