Valid from: 17.09.2018

EPIC<sup>®</sup> H-A 10 SDR-LB



### Description

- These connectors are attractive because of their compact housing.
- Small and space-saving for narrow available space



#### **General characteristics**

Series	H-A 10
Version	Surface-mount base
Locking	single lever
Protection cover	yes
Cable entry, direction	lateral
Cable entry, quantity	1
Protection (DIN EN 60529)	IP 65 (latched)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature range	-40°C to +100°C, short-term up to +125°C

### **Product variations**

Article no.	Thread
70455200	PG 16
70455400	PG 21

# Materials and surfaces

Housing Protection cover Lever Gasket	Aluminium alloy, powder-coated, grey Zinc alloy, powder-coated, grey Steel, zinc-plated NBR
Approvals	
VDE-Approval, VDE-REGNr.	B437
Standards	
Safety Standard	IEC 61984

Creator: MANA2/PDP	Document: DB70455200EN	Dece 1 of 2	
Released: IVSE1/PDP	Version: 01	Page 1 of 2	
We reserve all rights according to DIN ISO 16016			

# **DATA SHEET**


Valid from: 17.09.2018


EPIC<sup>®</sup> H-A 10 SDR-LB



## Drawings











Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info Compact, robust metal housings size H-A 10

### Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB70455200EN		
Released: IVSE1/PDP	Version: 01	Page 2 of 2	
We reserve all rights according to DIN ISO 16016			