#### 75009622

## **DATA SHEET**

Valid from: 14.01.2019

 $\mathsf{EPIC}^{\circledR}\,\mathsf{KIT}\,\mathsf{H-A}\,\mathsf{4}\;\mathsf{BS}\;\mathsf{MAGSV}\;\mathsf{M20}\;\mathsf{ZW}$ 



### Description

- H-A inserts, easy to service, with screw termination up to 2.5 mm<sup>2</sup> wire cross section
- The small H-A is used whenever there is minimal space
- Easy cable connection with strait cable entry in the contacts.
- Optimally matched components
- Reduced ordering effort
- No wrong orders





### Components of the combination

Article number of the combination 75009622

Housing H-A 3 MAgsv M20 ZW (19512700)

Insert H-A 4 BS (10432000)

#### General characteristics

Series H-A 4
Version Female

Connection type Screw termination

Pin-arrangement 4 + PE Contact diameter 1 mm

Termination cross section Screw termination: 0,5 – 2,5 mm² (2,5 mm² with wire end sleeve,

depending on crimp profile)

Degree of protection (DIN EN 60529) IP 65 (latched)
Degree of protection (NEMA 250/UL 50E) 12, 4 (latched)

Cycles of mechanical operation 100

Temperature range -40°C to +125°C, short term up to +125

#### Materials and surfaces

Housing Zinc die-casting surface Housing Powder-coating, grey

Insert P.

Contact, base material Copper alloy Contact, surface Hard-silver

#### **Electrical characteristics**

Rated Voltage, IEC 400 V
Rated Voltage, UL 600 V
Rated Voltage, CSA 600 V
Rated Impulse Voltage 4 kV
Rated Current, IEC 23 A
Rated Current, UL 10 A
Rated Current, CSA 10 A

Contact Resistance 1,5 - 4 mOhm

Degree of Soiling

Creator: JOKR1/PDP	Document: DB75009622EN	Page 1 of 3
Released: IVSE1/PDP	Version: 01	

# **DATA SHEET**

Valid from: 14.01.2019

75009622

# $\mathsf{EPIC}^{\scriptscriptstyle{(\! R)}}\,\mathsf{KIT}\,\,\mathsf{H-A}\,\,\mathsf{4}\,\,\mathsf{BS}\,\,\mathsf{MAGSV}\,\,\mathsf{M20}\,\,\mathsf{ZW}$



### **Approvals**

VDE-Approval, VDE-REG.-Nr. B437 UL File Number E75770 CSA File Number 053004








#### **Standards**


Safety Standard IEC 61984; UL 1977; CSA-C22.02

## **Technical Drawings**


### Housing



Insert







Creator: JOKR1/PDP	Document: DB75009622EN	Page 2 of 3
Released: IVSE1/PDP	Version: 01	

# 75009622 DATA SHEET

Valid from: 14.01.2019

# $\mathsf{EPIC}^{\scriptscriptstyle{(\! R)}}\,\mathsf{KIT}\,\,\mathsf{H-A}\,\,\mathsf{4}\,\,\mathsf{BS}\,\,\mathsf{MAGSV}\,\,\mathsf{M20}\,\,\mathsf{ZW}$





Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Assembly time



Space requirement

#### Info

Compact, robust metal housings size H-A 3 Robust power supply connector Straight cable entry into the contacts

### **Application range**

Machine and equipment manufacturing Control engineering Electronic laboratory

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.