79092200	DATA SHEET
Valid from:	EPIC [®] H-B 16 TBFH-LB



Description

17.09.2018

- The housing standard.
- Wide choice for all applications.



General Characteristics

Series H-B 16

Version Cable coupler hood M25 / M32 (Article 79092400)

Gland body

Single lever Locking Cable entry Straight

Protection (DIN EN 60529) IP 65 (latched) Protection (NEMA 250, UL50E) 12 (latched)

Temperature Range -40°C to +100°C, short term up to +125°C

Materials and Surfaces

Housing Aluminium alloy, powder-coated, grey Bolt Heat-treatable steel, zinc-plated

Lever Steel, zinc-plated

Sealing **NBR**

Approvals

VDE-Approval, VDE-REG.-Nr. B437

Standard

IEC 61984 Safety Standard

79092200 DATA SHEET


EPIC[®] H-B 16 TBFH-LB



Valid from: 17.09.2018

Technical Drawings









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

Application range

Plant engineering Light & sound technology Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB79092200EN	Page 2 of 2
Released: IVSE1/PDP	Version: 01	