# **DATA SHEET**

Valid from: 17.09.2018

EPIC<sup>®</sup> H-B 16 SDRLH-BO



### Description

- The housing standard.
- Wide choice for all applications.



## **General Characteristics**

Series	Н-В 16
Version	Surface mount base M25 / M32 (Article 79096400)
Protection cover	Yes
Locking	Bolts for double lever
Cable entry	2
Protection (DIN EN 60529)	IP 65 (latched) IP 40 (cover closed)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C
Materials and Surfaces	

Housing Cover Bolt Sealing	Aluminium alloy, powder-coated, grey Zinc alloy, powder-coated grey Zinc-plated steel NBR
Approvals	
VDE-Approval, VDE-REGNr.	B437

#### Standard

Safety Standard

IEC 61984

Creator: MANA2/PDP	Document: DB79096200EN	Dogo 1 of 2		
Released: IVSE1/PDP	Version: 02	Page 1 of 2		
We reserve all rights according to DIN ISO 16016				




Valid from: 17.09.2018

EPIC<sup>®</sup> H-B 16 SDRLH-BO

## **Technical Drawings**









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

### Application range

Plant engineering Light & sound technology Plastics industry

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB79096200EN	Page 2 of 2		
Released: IVSE1/PDP	Version: 02			
We reserve all rights according to DIN ISO 16016				