# **DATA SHEET** 79164200 Valid from:

EPIC® H-B 24 SDRH-LB



## Description

17.09.2018

Ideal for many applications due to a wide range of housings and



### **General Characteristics**

Series H-B 24

Version Surface mount base M25 / M32 (Article 79164400)

Protection cover Yes

Single lever Locking

Cable entry 1

Protection (DIN EN 60529) IP 65 (latched) Protection (NEMA 250, UL50E) 12 (latched)

-40 °C to +100 °C, short term up to +125 °C Temperature Range

### **Materials and Surfaces**

Housing Aluminium alloy, powder-coated, grey Cover Zinc alloy, powder-coated, grey Bolt Heat-treatable steel, zinc-plated

Steel, zinc-plated Lever

Sealing **NBR** 

## **Approvals**

VDE-Approval, VDE-REG.-Nr. B437

### **Standard**

Safety Standard IEC 61984


# 79164200 DATA SHEET

Valid from: 17.09.2018 EPIC® H-B 24 SDRH-LB



## **Technical Drawings**









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

## Info

Universal, robust metal housings size H-B 24

# **Application range**

Plant engineering Light & sound technology Plastics industry

# Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB79164200EN	Page 2 of 2
Released: IVSE1/PDP	Version: 01	