79462200	DATA SHEET	
Valid from: 17.09.2018	EPIC [®] H-A 10 TSH	



Description

- These connectors are attractive because of their compact housing.
- Small and space-saving for narrow available space



General characteristics

Series H-A 10

Version Hood, high version
Locking Bolts for single lever

Cable entry lateral

Protection (DIN EN 60529) IP 65 (latched)
Protection (NEMA 250, UL50E) 4, 12 (latched)

Temperature range -40°C to +100°C, short-term up to +125°C

Product variations

Article no.	Thread
79462200	M20
79462400	M25

Materials and surfaces

Housing Aluminium alloy, powder-coated, grey
Bolts Heat-treatable steel, zinc-plated

Gasket

Approvals

VDE-Approval, VDE-REG.-Nr. B437


Standards


Safety Standard IEC 61984

79462200 **DATA SHEET**Valid from: 17.09.2018 **EPIC® H-A 10 TSH**

Drawings











Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Compact, robust metal housings size H-A 10

Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB79462200EN	Page 2 of 2
Released: IVSE1/PDP	Version: 01	