# 22260221

# **DATA SHEET**

Valid from: 17.09.2018

AB-C3-M12MS-(L\*)PUR



### Description

• Sensor/actuator cable, 3-pos., PUR black

• straight plug M12 on free conductor end



#### **General characteristics**

Connection method M12-plug, A-standard

Number of pins 3

Ambient temperature -25 °C to +90 °C (-13 °F to +174°F) (connector)

-40 to +80 °C (-40°F to 176°F) (cable fixed installation)

-20 to +80 °C (-4°F to 176°F) (cable flexible)

IP65/IP67/IP68

Cut-off length of the free cable end 50 mm
Tightening torque 0.4 Nm

## **Product variations**

Degree of protection

Article number	Article description	Length (L*) [m]
22260221	AB-C3-M12MS-2,0PUR	2
22260222	AB-C3-M12MS-5,0PUR	5
22260249	AB-C3-M12MS-10,0PUR	10

٧

This datasheet is also valid for other length configurations. Other lengths upon request.

## **Electrical properties**

Rated voltage	250
Rated current	4 A
Overvoltage category	П
Pollution degree	3

#### **Mechanical properties**

## Plug

Inflammability class in accordance with UL 94 HB
Material, Contact carrier TPU GF
Material, Contact CuSn
Contact surface Ni/Au

Material, Handle TPU, flame retardant, self-extinguishing

Material, Knurl zinc diecasting, nickel-plated

Material, Sealing NBR

Creator: FELI1/PDP	Document: DB22260221EN	Daga 1 of 2
Released: IVSE1/PDP	Version: 06	Page 1 of 2

# 22260221

# **DATA SHEET**

# Valid from: 17.09.2018

# AB-C3-M12MS-(L\*)PUR



#### Line

Cable construction

Conductor diameter including isolation

Cable outer diameter Core identification

Sheath color Bending radius

Number of bending cycles

Travel length
Travel speed
Cable weight

Outer coating, material Material wire insulation Flame resistance

Halogen-free Oil resistance

Standards/Approvals

Product standard, M12 connector

UL-listed, E-File

3xAWG22/42

1.27 mm ± 0.02mm

4.4 mm ± 0.15mm

brown, blue, black

grey-black, similar to RAL 7021

44 mm 4.000.000 10 m 3 m/s 26 kg / km

PUR PP


acc. UL-style 20549

acc. to DIN VDE 0472 Teil 815 acc. to DIN EN 60811-2-1

IEC 61076-2-101


E249137

## **Technical drawings**




Pin assignment M12-plug, 3 pol, A-coding

Circuit Diagram







Plug M12x1, straight

# Application range

Automation, industrial machinery and plant engineering

Pin assignment M12 plug

#### Noto

Photographs are not true to scale and do not represent detailed images of the respective products

BN

BK

Creator: FELI1/PDP	Document: DB22260221EN	Daga 2 of 2
Released: IVSE1/PDP	Version: 06	Page 2 of 2