

24441256	DATA SHEET
Valid from: 15.12.2020	RJ45 Stecker TM31 Hirose Cat.6_A C*

Description

- RJ45 plug
- Cat. 6_A
- RoHS conform



General characteristics

Connector RJ45
 Temperature range -25 °C to 60 °C (Operation und Storage)

Variation

Article	Description	Color (C*)
24441256	RJ45 Stecker TM31 Hirose Cat.6A GY	GY (= grey)
24441257	RJ45 Stecker TM31 Hirose Cat.6A BG	BG (= beige)
24441258	RJ45 Stecker TM31 Hirose Cat.6A BK	BK (= black)
24441259	RJ45 Stecker TM31 Hirose Cat.6A RD	RD (= red)
24441260	RJ45 Stecker TM31 Hirose Cat.6A GN	GN (= green)
24441261	RJ45 Stecker TM31 Hirose Cat.6A BU	BU (= blue)
24441262	RJ45 Stecker TM31 Hirose Cat.6A YE	YE (= yellow)

Mechanical characteristics

Mounting cycles (min.) 750

Electrical characteristics

Rated voltage 125 V AC
 Current carrying capacity 1 A

Applicable cable

Conductor AWG24 to AWG26
 Insulator outer Ø Ø0.9 to Ø 1.0
 Jacket outer diameter Ø 5.8 to Ø 6.0

Note

Photographs are not to scale and do not represent detailed images of the respective products.