

55507340	<b>DATA SHEET</b>	
Valid from: 03.07.2018	<b>SILVYN® FPAX T</b>	

SILVYN® FPAX T is a T-hook conduit gland and cable distributor with fast fit and an inner seal for a safety assembling. For the demounting we are recommending to use a screwdriver. The gland is suitable for SILVYN® FPAS and can be used in the machine- and plant constructions.



**Material:** Body – PA66  
Seal – Polyester

**Features:** Fast assembling  
Anti-vibration  
Suitable for fine and coarse conduits  
High mechanical strength

**Temperature range:** -50°C up to +135°C

**Colour:** Black (UV-Resistant)

**Norm Reference:**



**Note:** Free of halogen, Sulphur and phosphorus

**Protection class:** IP66, IP67 and IP68 (2bar)

**Dimension table:**

Part no.	Part name	Conduit Ø mm	Cable Ø mm	wide mm	height mm	Holes distance mm	Ø holes mm
5550 7340	SILVYN® FPAX T	16	14	96	62	33	6,2
5550 7341	SILVYN® FPAX T	21	19	99	63	34	6,2
5550 7342	SILVYN® FPAX T	28	25	125	87	45	6,0
5550 7343	SILVYN® FPAX T	34	33	130	91	48	7,2
5550 7344	SILVYN® FPAX T	42	41	150	110	55	7,2

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Wegerer /PDP Released: DAMU1/PDP	Document: DB55507340EN Version: 01	Page 1 of 1
---	---------------------------------------	-------------