


6181 5100	<b>DATA SHEET</b>	
Valid from: 14.05.2018	<b>SILVYN® RILL PA 12</b>	

The conduit SILVYN® RILL PA 12 is suitable for various uses due to his characteristics. The conduit is qualified for protective insulation for electrical installation in acc.to instruction for use EN 60204 at engineering and plant construction, especially for frequent reversed bending, e. g. for robots.



**Material:**

Polyamide 12

**Technical features:**

Profile

Parallel corrugated

Nominal size

NW 10 up to NW 54

Protection class

IP67 acc. to EN 60529

Depending on the used conduit gland

Temperature range

-50°C up to +100°C

**Additional features:**

Compressive strength

Class 1 (125N) acc. to EN 61386

Impact strength

Class 1 (0,5kg) acc. to EN 61386

Bending resistance

Flexible

Tensile strength

Class 1 (100N) acc. to EN 61386

Fire classification

V2 acc. to UL94

Free of silicone, cadmium and halogen

UV-Resistant

SILVYN® RILL PA 12 black

**Color:**

Black

Grey

**Approbation:**



E-File E308201



**Reference standards:**

EN 61386-23

**Suitable glands:**


SILVYN® KCLICK

SILVYN® KSE


SILVYN® K-EM

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: MAU1/PDP Released: DAMU1/PDP	Document: DB61815100EN Version: 04	Page 1 of 2
--	---------------------------------------	-------------

6181 5100	<b>DATA SHEET</b>	
Valid from: 14.05.2018	<b>SILVYN® RILL PA 12</b>	

**Product drawing:**



**Dimension table:**

Part No.	NW	Diameter mm		Max. Bending radius mm		Weight kg/m
		$\phi I$	$\phi A$	static	dynamic	
<b>SILVYN® RILL PA 12 black</b>						
6181 5105	10	6,5	10,0	13	35	0,018
6181 5115	13	10,0	13,0	15	45	0,024
6181 5125	16	12,0	15,8	22	55	0,034
6181 5185	18	14,3	18,5	27	65	0,050
6181 5135	21	16,5	21,2	35	75	0,056
6181 5145	28	23,0	28,5	45	100	0,090
6181 5155	34	29,0	34,5	50	120	0,120
6181 5165	42	36,0	42,5	80	150	0,165
6181 5175	54	48,0	54,5	100	190	0,225
<b>SILVYN® RILL PA 12 grey</b>						
6181 5100	10	6,5	10,0	13	35	0,018
6181 5110	13	10,0	13,0	15	45	0,024
6181 5120	16	12,0	15,8	22	55	0,034
6181 5180	18	14,3	18,5	27	65	0,050
6181 5130	21	16,5	21,2	35	75	0,056
6181 5140	28	23,0	28,5	45	100	0,090
6181 5150	34	29,0	34,5	50	120	0,120
6181 5160	42	36,0	42,5	80	150	0,165
6181 5170	54	48,0	54,5	100	190	0,225