

68100100	DATA SHEET	
Valid from: 03.07.2018	SILVYN® FLEXILOK 90° M	

SILVYN® FLEXILOK 90° M is a one-part conduit gland with fast fit for a safety assembling. For the demounting we are recommending to use a screwdriver. The gland is suitable for SILVYN® FPAS and can be used in the machine- and plant constructions, control cabinet and building wiring.




Material: PA66

Features: Fast assembling
Slim design
Suitable for fine and coarse conduits

Temperature range: -40°C up to +120°C

Colour: Grey (RAL 7031)
Black (UV-Resistant)

Norm reference: 
UL FILENUMBER E308201

Note: Free of halogen, silicon and cadmium

Protection class: IP 66

Dimension table:

Part no.	Part name	Thread	Conduit Ø mm	Total length mm	Thread length mm	Outer Ø mm	Inner Ø mm
Black							
6810 0100	SILVYN® FLEXILOK 90° M	M 16x1,5	16	44,5	11,5	21	10,5
6810 0105	SILVYN® FLEXILOK 90° M	M 20x1,5/1	16	46	13	21	14
6810 0110	SILVYN® FLEXILOK 90° M	M 20x1,5/2	21	49	13	26	14
6810 0115	SILVYN® FLEXILOK 90° M	M 25x1,5	28	60	15	34	19
6810 0120	SILVYN® FLEXILOK 90° M	M 32x1,5	34	69	16	41	24,5
Grey							
6810 0125	SILVYN® FLEXILOK 90° M	M 16x1,5	16	44,5	11,5	21	10,5
6810 0130	SILVYN® FLEXILOK 90° M	M 20x1,5/1	16	46	13	21	14
6810 0135	SILVYN® FLEXILOK 90° M	M 20x1,5/2	21	49	13	26	14
6810 0140	SILVYN® FLEXILOK 90° M	M 25x1,5	28	60	15	34	19
6810 0145	SILVYN® FLEXILOK 90° M	M 32x1,5	34	69	16	41	24,5

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Wegerer /PDP Released: DAMU1/PDP	Document: DB68100100EN Version: 02	Page 1 of 1
---	---------------------------------------	-------------