



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No.: 2021312313000439

Applicant	U.I. Lapp GmbH
Address	Schulze-Delitzsch-Straße 25, 70565 Stuttgart, Germany
Manufacturer	U.I. Lapp GmbH
Address	Schulze-Delitzsch-Straße 25, 70565 Stuttgart, Germany
Production Factory	U.I. Lapp GmbH
Production Address	Schulze-Delitzsch-Straße 25, 70565 Stuttgart, Germany
Product	Blanking plug
Model/Type	SKINDICHT® BL-M** ATEX ***
Ex marking	Ex eb IIC Gb, Ex ta IIIC Da
Reference Standards	GB/T 3836.1-2021, GB/T 3836.3-2021, GB/T 3836.31-2021

Certification mode Type Test + Initial Factory Inspection + Post-Certification Surveillance

The product(s) is verified and certified according to CNCA-C23-01: 2019 *China Compulsory Certification Implementation Rule on Explosion Protected Electrical Product* and CNEX-C2301-2019 *Guideline of China Compulsory Certification Implementation Rule on Explosion Protected Electrical Product*.

See Annex for the detailed product information (2 pages).

Initial issue date: 2021-01-27

Issued date: 2023-04-29

Valid to: 2026-01-26

The validity of this certificate is maintained through the regular supervision of the issuing authority during the validity period.

Where any discrepancy arises between the English translation and the original Chinese version, the Chinese version shall prevail.

Director:



Nanyang Explosion Protected Electrical Apparatus Research Institute Co., Ltd.



<http://www.ccc-cnex.com>
ccc.china-ex.com

Add: No. 20, North Zhongjing Road, Nanyang, Henan, P. R. China P.C.: 473008
Tel: 0377-63239734 Email: ccc@cn-ex.com

CN 0001937



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION (Annex)

No.: 2021312313000439

Page 1 of 2

Product information:

1. This certificate covers the following models:

- SKINDICHT® BL-M** ATEX ***

Type designation	Thread size
SKINDICHT® BL-M 12-ATEX ***	M12 × 1.5
SKINDICHT® BL-M 16-ATEX ***	M16 × 1.5
SKINDICHT® BL-M 20-ATEX ***	M20 × 1.5
SKINDICHT® BL-M 25-ATEX ***	M25 × 1.5
SKINDICHT® BL-M 32-ATEX ***	M32 × 1.5
SKINDICHT® BL-M 40-ATEX ***	M40 × 1.5
SKINDICHT® BL-M 50-ATEX ***	M50 × 1.5
SKINDICHT® BL-M 63-ATEX ***	M63 × 1.5

*** = Manufacturer's indications without special meaning for the explosion protection
(e. g. longer connection threads)

Rated service temperature range: -30°C~+90°C

Degree of protection: IP66, IP68 (10bar/30min)

Ex marking: Ex eb IIC Gb, Ex ta IIIC Da

- Producers should organize production in accordance with the technical documents approved by the certification body.

2. Specific conditions of safety use:

Issued date: 2023-04-29

Director:



Nanyang Explosion Protected Electrical
Apparatus Research Institute Co.,Ltd.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION (Annex)

No.: 2021312313000439

Page 2 of 2

- The service temperature must not exceed 90°C.
 - See instruction for other information.
3. Certificate related report(s):
- Type test report: CQST2105C032, CQST2105C032/01
 - Factory inspection report: CN2021Q010433
4. Certificate change information:
- 1st change on April 29, 2023:
Updated the standards for certification.

Issued date: 2023-04-29

Director:



Nanyang Explosion Protected Electrical
Apparatus Research Institute Co.,Ltd.

