

11190000	DATA SHEET	
Valid from: 16.11.2018	EPIC® H-BE 2.5 CONTACTS MACHINED	

Description

- For inserts and modules of the EPIC® rectangular connectors



Article-Number	Article	Version	Conductor cross-section (mm ²)	Cross-section ratio	Surface	Stripping length (mm)
11190000	H-BE 2.5	male	0,5	0	Ag	7,4
11195000	H-BE 2.5	female	0,5	0	Ag	7,3
11190100	H-BE 2.5	male	0,75 - 1	1	Ag	7,4
11195100	H-BE 2.5	female	0,75 - 1	1	Ag	7,3
11190200	H-BE 2.5	male	1,5	2	Ag	7,4
11195200	H-BE 2.5	female	1,5	2	Ag	7,3
11190300	H-BE 2.5	male	2,5	3	Ag	7,4
11195300	H-BE 2.5	female	2,5	3	Ag	7,3
11190400	H-BE 2.5	male	4,00		Ag	7,4
11195400	H-BE 2.5	female	4,00		Ag	7,3
11192000	H-BE 2.5	male	0,5	0	Au	7,4
11197000	H-BE 2.5	female	0,5	0	Au	7,3
11192100	H-BE 2.5	male	0,75 - 1	1	Au	7,4
11197100	H-BE 2.5	female	0,75 - 1	1	Au	7,3
11192200	H-BE 2.5	male	1,5	2	Au	7,4
11197200	H-BE 2.5	female	1,5	2	Au	7,3
11190301	H-BE 2,5	Stift	0,14-0,37	1	Au	7,4
11190302	H-BE 2,5	Buchse	0,14-0,37	1	Au	7,3



Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB11190000EN Version: 03	Page 1 of 1
-------------------------------------------	---------------------------------------	-------------