

|                           |                            |                                                                                     |
|---------------------------|----------------------------|-------------------------------------------------------------------------------------|
| 19426000                  | <b>DATA SHEET</b>          |  |
| Valid from:<br>17.09.2018 | <b>EPIC® H-A 3 Tgv M20</b> |                                                                                     |

## Description

- Innovative metal and plastic housing design
- Housing in plastic or metal version. For power supply in the smallest possible space



## General characteristics

|                              |                                          |
|------------------------------|------------------------------------------|
| Series                       | H-A 3                                    |
| Version                      | Hood M20                                 |
| Locking mechanism            | bolts for single lever                   |
| Cable entry                  | straight                                 |
| Protection (DIN EN 60529)    | IP 65 (latched)                          |
| Protection (NEMA 250, UL50E) | 4, 12 (latched)                          |
| Temperature range            | -40°C to +100°C, short-term up to +125°C |

## Materials and surfaces

|         |          |
|---------|----------|
| Housing | PA, grey |
|---------|----------|

## Approvals

|                            |      |
|----------------------------|------|
| VDE-Approval, VDE-REG.-Nr. | B437 |
|----------------------------|------|


## Standards

|                 |                    |
|-----------------|--------------------|
| Safety Standard | IEC 61984; UL 1977 |
|-----------------|--------------------|

|                                           |                                       |             |
|-------------------------------------------|---------------------------------------|-------------|
| Creator: MANA2/PDP<br>Released: IVSE1/PDP | Document: DB19426000EN<br>Version: 01 | Page 1 of 2 |
|-------------------------------------------|---------------------------------------|-------------|

|                           |                     |                                                                                     |
|---------------------------|---------------------|-------------------------------------------------------------------------------------|
| 19426000                  | <b>DATA SHEET</b>   |  |
| Valid from:<br>17.09.2018 | EPIC® H-A 3 Tgv M20 |                                                                                     |

## Drawings



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

### Info

Compact, robust housings size H-A 3

### Application range

Machine and equipment manufacturing  
Control engineering  
Electronic laboratory

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

|                                           |                                       |             |
|-------------------------------------------|---------------------------------------|-------------|
| Creator: MANA2/PDP<br>Released: IVSE1/PDP | Document: DB19426000EN<br>Version: 01 | Page 2 of 2 |
|-------------------------------------------|---------------------------------------|-------------|