

52002827	<b>DATA SHEET</b>	
Valid from: 03.07.2018	<b>SILVYN<sup>®</sup> SSV-M</b>	

The SILVYN<sup>®</sup> SSV-M is a conduit clamp gland from nickel-plated brass. Special design of snap-in noses on the hose nipple ensures easy assembling and optimal strain relief of the conduit gland.  
The SILVYN<sup>®</sup> SSV-M can be combined with the hose clip SILVYN<sup>®</sup> SCH for additional strength.



### Components:

Conduit gland body	Brass, nickel-plated
O-ring	NBR

### Technical features:

Connecting thread	M12x1,5 up to M63x1,5 acc.to EN 60423
Protection class	IP54 up to IP68 acc. to EN 60529
Temperature range	-20 °C up to +80 °C

### Suitable protective Cable conduit:

SILVYN<sup>®</sup> SI - IP68  
SILVYN<sup>®</sup> SP - IP54  
SILVYN<sup>®</sup> SP-PU - IP54

### Accessories:

Hose clip SILVYN<sup>®</sup> SCH

### Properties:


Hose nipple with special grip profile  
Tensile strength  
Robust  
Compact design

### Norm references:



Creator: V.Charcenko /PDP Released: DAMU1/PDP	Document: DB52002827EN Version: 02	Page 1 of 2
--	---------------------------------------	-------------

52002827	<b>DATA SHEET</b>	
Valid from: 03.07.2018	<b>SILVYN® SSV-M</b>	



**Dimension table:**

Article No.	Description	M	SW	D [mm]	C [mm]	Ø B [mm]	Ø E [mm]
52002827	SSV-M12x1,5/1	M12x1,5	16	8	25	7	9,3
52002828	SSV-M12x1,5/2	M12x1,5	19	8	25	9	12,3
52002840	SSV-M16x1,5/1	M16x1,5	19	8	25	8	10,3
52002839	SSV-M16x1,5/2	M16x1,5	19	8	25	10	12,3
52002841	SSV-M20x1,5/1	M20x1,5	22	8	25	12	14,3
52002842	SSV-M20x1,5/3	M20x1,5	25	8	25	15,5	18,3
52002843	SSV-M25x1,5	M25x1,5	32	8,5	29,5	19	22,2
52002844	SSV-M32x1,5	M32x1,5	40	9,5	32,5	27	30,3
52002845	SSV-M40x1,5	M40x1,5	50	11	36	34	38,3
52002846	SSV-M50x1,5	M50x1,5	57	12	39	41	45,3
52002847	SSV-M63x1,5	M63x1,5	67	12	43	46	50

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: V.Charcenko /PDP Released: DAMU1/PDP	Document: DB52002827EN Version: 02	Page 2 of 2
--	---------------------------------------	-------------