

52104800	DATA SHEET	
Valid from: 03.07.2018	SKINDICHT® SVRN-M	

The SKINDICHT® SVRN-M brass cable gland is a cable entry for the universal use. The gland with hexagonal fitting offers a fast assembly with a flat spanner.



Components:

Gland body	Brass, nickel-plated
Pressure screw	Brass, nickel-plated
Pressure washers	Steel, zinc-plated
Sealing ring	CR

Technical features:


Connecting thread	M12x1.5 up to M40x1.5 acc. to EN 60423
Functions thread	PG-thread acc. to DIN 40430
Protection class	IP54 acc. to EN 60529
Temperature range	-20 °C up to +100 °C

Norm references:



Creator: V. Charcenko /PDP Released: DAMU1/PDP	Document: DB52104800EN Version: 02	Page 1 of 2
---	---------------------------------------	-------------

52104800	DATA SHEET	
Valid from: 03.07.2018	SKINDICHT® SVRN-M	



M Connecting thread	PG Function thread	Ø F [mm]	SW1 / SW2 [mm]	C [mm]	Ø E [mm]	D [mm]	Article No.
M12x1,5	PG7	5	14 / 13	20,6	15,5	5	52104800
M12x1,5	PG7	6	14 / 13	20,6	15,5	5	52104810
M12x1,5	PG7	7	14 / 13	20,6	15,5	5	52104820
M16x1,5	PG9	7	18 / 15	21,6	20	5	52104830
M16x1,5	PG9	8	18 / 15	21,6	20	5	52104840
M16x1,5	PG9	9	18 / 15	21,6	20	5	52104850
M20x1,5	PG11	10	22 / 18	23,6	24	6	52104860
M20x1,5	PG11	11	22 / 18	23,6	24	6	52104870
M20x1,5	PG13,5	11	22 / 20	25,1	24	6	52104880
M20x1,5	PG13,5	12	22 / 20	25,1	24	6	52104890
M20x1,5	PG16	13	24 / 22	26,1	26,2	6	52104900
M20x1,5	PG16	14	24 / 22	26,1	26,2	6	52104910
M25x1,5	PG21	18	30 / 28	29,6	33	7	52104920
M32x1,5	PG29	27	40 / 37	32,6	42,5	8	52104930
M40x1,5	PG36	34	50 / 47	37,6	54	8	52104940

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: V. Charcenko /PDP Released: DAMU1/PDP	Document: DB52104800EN Version: 02	Page 2 of 2
---	---------------------------------------	-------------