


55503179	DATA SHEET	
Valid from: 03.07.2018	SILVYN® LGEP	

SILVYN® LGEP is a two part protection connector for conduits made of nickel plated brass. The connector is suitable for SILVYN® SSUE and can be used in offshore applications and in demanding mechanical environments.



- Material:** Nickel plated brass
- Features:** High mechanical resistant
Oil resistant
Corrosion resistant
Conforms to DIN EN 61386
- Temperature range:** -50 up to +300 °C
- Protection class:** IP 40
- Suitable conduit:** SILVYN® SSUE



Dimension table:

Part No.	Part name	Nominal size	Length mm	Inner Ø mm	SW
5550 3179	SILVYN® LGEP	10	15	5,6	13
5550 3180	SILVYN® LGEP	12	15,5	8,5	17
5550 3181	SILVYN® LGEP	16	20	11,5	20
5550 3182	SILVYN® LGEP	20	16,5	15,3	24
5550 3183	SILVYN® LGEP	25	20,5	19,1	29
5550 3184	SILVYN® LGEP	32	23,5	26,2	38
5550 3185	SILVYN® LGEP	40	24,8	34,2	48
5550 3186	SILVYN® LGEP	50	30	44,8	58
5550 3187	SILVYN® LGEP	63	33,5	54,5	70
5550 3188	SILVYN® LGEP	75	42	66,5	84

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Wegerer /PDP Released: DAMU1/PDP	Document: DB55503179EN Version: 01	Page 1 of 1
---	---------------------------------------	-------------