

| | | |
|---------------------------|-----------------------|---|
| 55507350 | DATA SHEET |  |
| Valid from: 03.07.2018 | SILVYN® FPAX Y | |

SILVYN® FPAX Y is a Y-hook conduit gland with fast fit and an inner seal for a safety assembling. For the demounting we are recommending to use a screwdriver. The gland is suitable for SILVYN® FPAS and can be used in the machine- and plant constructions.



- Material:** Body – PA66
Seal – Polyester
- Features:** Fast assembling
Anti-vibration
Suitable for fine and coarse conduits
High mechanical strength
- Temperature range:** -50°C up to +135°C
- Colour:** Black (UV-Resistant)

Norm Reference:    

Note: Free of halogen, Sulphur and phosphorus

Protection class: IP66, IP67, IP68 (2bar) and IP69 K

Dimension table:

| Part no. | Part name | Conduit Ø | | Total | | holes | |
|-----------|----------------|-------------------|--------------------|--------------|------------|----------------|---------|
| | | Input value mm | Output value mm | length mm | wide mm | distance mm | Ø mm |
| 5550 7350 | SILVYN® FPAX Y | 16 | 2x13 | 77 | 49 | 24 | 4 |
| 5550 7351 | SILVYN® FPAX Y | 21 | 2x16 | 89 | 59 | 32 | 5 |
| 5550 7352 | SILVYN® FPAX Y | 28 | 2x21 | 93 | 67 | 49 | 6 |
| 5550 7353 | SILVYN® FPAX Y | 34 | 2x28 | 116 | 90 | 48 | 6,5 |

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

| | | |
|---|---------------------------------------|-------------|
| Creator: M. Wegerer /PDP Released: DAMU1/PDP | Document: DB55507350EN Version: 01 | Page 1 of 1 |
|---|---------------------------------------|-------------|