

55507370	DATA SHEET	
Valid from: 03.07.2018	SILVYN® FPAX P	

SILVYN® FPAX P is a plug for SILVYN® FPAX T and Y Systems.



- Material:** PA66
- Features:** Fast assembling
Safety clasp to water and dust
- Temperature range:** -50°C up to +135°C
- Colour:** Black (UV-Resistant)

Norm Reference: 

Note: Free of halogen, Sulphur and phosphorus

Protection class: IP66, IP67 und IP68 (2bar)

Dimension table:

Part no.	Part name	Conduit Ø mm	Total height mm	Height of head mm	Head Ø mm
5550 7370	SILVYN® FPAX P	16	25,5	5	27,6
5550 7371	SILVYN® FPAX P	21	27,5	5	33,6
5550 7372	SILVYN® FPAX P	28	33,5	5	42,2
5550 7373	SILVYN® FPAX P	34	34,8	5	48,5

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Wegerer /PDP Released: DAMU1/PDP	Document: DB55507370EN Version: 01	Page 1 of 1
---	---------------------------------------	-------------