


56000120	DATA SHEET	
Valid from: 03.07.2018	SILVYN® KLICK-Y (TPE)	

SILVYN® KLICK-Y (TPE) is a one-part Y-formed conduit distributor. The distributor has three conduit connectors for a simple and safety assembling and disassembling. SILVYN® KLICK-Y (TPE) fits to the conduit SILVYN® RILL and can by one M4 screws easily mounted.



- Material:** Body – TPE
- Feature:** Rational tubing assembly
Assembled by just putting on
- Temperature range:** -40°C up to +120°C, for short term +150°C
- Colour:** Grey RAL 7001
Black (UV-resistance)

Norm Reference: 
UL FILENUMBER E308201

Protection class: IP 66

Dimension table:

Part No.	Nominal size AD 1	Nominal size AD 2	Outer Ø B1 mm	Outer Ø B2 mm	Total wide C mm	Length D mm	Screw hole mm
SILVYN KLICK-Y (TPE) – grey							
5600 0120	1 x 10	2 x 10	17,5	17,5	36,5	54,5	1 x 4,0
5600 0140	1 x 21	2 x 16	29,5	25	52	75	1 x 4,0
5600 0150	1 x 28	2 x 21	36,5	29,5	60,5	81,5	1 x 4,0
5600 0160	1 x 34	2 x 28	42,5	36,5	77	86	1 x 4,0
SILVYN KLICK-Y (TPE) – black							
5600 0125	1 x 10	2 x 10	17,5	17,5	36,5	54,5	1 x 4,0
5600 0145	1 x 21	2 x 16	29,5	25	52	75	1 x 4,0
5600 0155	1 x 28	2 x 21	36,5	29,5	60,5	81,5	1 x 4,0
5600 0165	1 x 34	2 x 28	42,5	36,5	77	86	1 x 4,0

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Wegerer /PDP Released: DAMU1/PDP	Document: DB56000120EN Version: 03	Page 1 of 1
---	---------------------------------------	-------------