

61723360	DATA SHEET
Valid from: 04.02.2020	Detectable Cable ties without steel nose

The detectable cable ties are made of polyamide and can be used in many different applications, due to his features. Due to his material features, the cable tie can be detected by different systems.



Material: Polyamide 6.6 with iron oxide

Technical Features:

Bundle diameter 1 up to 102mm
 Bandwidth 2,5 up to 7,5 mm
 Tensile strength 80 up to 540N

Additional features:


Fire Classification HB acc. to UL 94
 Resistant to Solvents, oils and greases
 Detected by X-Ray inspection equipment, metal detector and optical identification systems

Temperature range: -40°C up to +85°C
 Installations temperature -5°C up to +65°C

Color: Blue



Norm Reference: EN 62275



Dimensions:

Part No.	Type	Bundeldiameter mm		Dimensions mm						Tensile strength N
		min	max	A	B	C	E	F	G	
61723360	A	1	21	98	2,5	1	4,65	4,65	3,8	80
61723364	A	2	32	140	3,55	1,09	6,1	6,3	4,7	180
61723365	A	3	50	200	3,5	1,2	6,1	5,8	4	180
61723361	A	3	50	200	4,5	1,35	7,8	7,25	5,35	220
61723366	B	3,5	78	290	4,5	1,4	7,75	7,15	5,3	220
61723362	B	3,5	100	360	4,5	1,4	7,8	7,15	5,3	220
61723363	B	8	100	365	7,5	1,8	12,8	11,3	7,5	540

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.