

6181 1200	DATA SHEET	
Valid from: 30.08.2019	SILVYN® KLICK-D	

SILVYN® KLICK-D is a cover for the conduit holder SILVYN® KLICK-S and prevented for disassembling.



Material: Polyamide 6

Technical Features:

Nominal wide NW 7 up to NW 48
 Temperature range -40°C up to +105°C

Additional features:

Fire classification V2 acc. to UL94
 Free of halogen und phosphorus
 UV-Resistant SILVYN® KLICK-D black

Colour: Grey
 Black



Approbation:

Suitable conduits: SILVYN® KLICK-S
 SILVYN® KLICK-V

Dimension table:

Part No.	Nominal width NW	Width mm	Plug distance mm	Cover High mm	High mm	Weight g
SILVYN® KLICK-D grey						
6181 1200	10/13	20,0	14,0	2,0	5,0	1,2
6181 1260	16	22,0	16,0	2,0	5,0	1,3
6181 1210	18/21	28,0	22,0	2,0	5,0	1,6
6181 1220	28	35,0	29,0	2,0	5,0	1,8
6181 1230	34	42,0	36,0	2,0	5,0	2,2
6181 1240	42	54,0	48,0	2,0	5,0	2,7
6181 1250	54	67,5	61,5	2,0	5,0	3,4
SILVYN® KLICK-D black						
6181 1205	10/13	20,0	14,0	2,0	5,0	1,2
6181 1265	16	22,0	16,0	2,0	5,0	1,3
6181 1215	18/21	28,0	22,0	2,0	5,0	1,6
6181 1225	28	35,0	29,0	2,0	5,0	1,8
6181 1235	34	42,0	36,0	2,0	5,0	2,2
6181 1245	42	54,0	48,0	2,0	5,0	2,7
6181 1255	54	67,5	61,5	2,0	5,0	3,4

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: MAU1/PDP Released: DAMU1/PDP	Document: DB61811200EN Version: 02	Page 1 of 1
--	---------------------------------------	-------------