

65500200	DATA SHEET	
Valid from: 03.07.2018	SILVYN® K-EM	

SILVYN® K-EM is an end cap for rational tubing assembly, with an optimal passage between protection conduit and cable.
The assembling will be made by simple putting on and prevent the cable for damage and dirt.



- Material:** TPE
- Features:** Easy to plug on
Free of silicone, cadmium, phosphor and halogen
Self-extinguishing
Flame class HB acc. to UL 94
Ozone resistant
- Resistance to:** Methanol, silicone grease, hydrogen and seawater
- Temperature range:** -40°C up to +120 °C, for short term +150°C
- Color:** Grey
Black (UV-Resistant)

Dimension table

Part No.	Nominal size	Length mm	Cable Ø mm		Weight kg / 100
			Min.	Max.	
SILVYN® K-EM grey					
6550 0200	10	29	1,0	8,0	0,16
6550 0210	13	29	1,0	10,0	0,22
6550 0220	15,8	36	4,0	12,0	0,32
6550 0230	21,2	37	6,0	16,5	0,56
6550 0240	28,5	40	6,0	23,0	0,8
6550 0250	34,5	44	6,0	29,0	0,96
6550 0260	42,5	46	10,0	37,0	1,48
6550 0270	54,5	53	10,0	47,0	2,3
SILVYN® K-EM black					
6550 0205	10	29	1,0	8,0	0,16
6550 0215	13	29	1,0	10,0	0,22
6550 0225	15,8	36	4,0	12,0	0,32
6550 0235	21,2	37	6,0	16,5	0,56
6550 0245	28,5	40	6,0	23,0	0,8
6550 0255	34,5	44	6,0	29,0	0,96
6550 0265	42,5	46	10,0	37,0	1,48
6550 0275	54,5	53	10,0	47,0	2,3

Suitable conduit: SILVYN® RILL

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Wegerer /PDP Released: DAMU1/PDP	Document: DB65500200EN Version: 03	Page 1 of 1
---	---------------------------------------	-------------