


|                           |                            |   |
|---------------------------|----------------------------|---|
| 65500475                  | <b>DATA SHEET</b>          |  |
| Valid from:<br>03.07.2018 | <b>SILVYN® FLEXILOK PG</b> |   |

SILVYN® FLEXILOK PG is a one-part conduit gland with fast fit for a safety assembling. For the demounting you are using a screwdriver. The gland is suitable for SILVYN® FPAS and can be used in the machine- and plant constructions, control cabinet and building wiring.



**Material:** PA66

**Features:** Fast assembling  
Slim design  
Suitable for fine and coarse conduits

**Temperature range:** -40°C up to +120°C

**Colour:** Grey (RAL 7031)  
Black (UV-Resistant)

**Norm reference:**    
UL FILENUMBER E308201

**Note:** Free of halogen, silicon and cadmium

**Protection class:** IP 66

**Dimension table:**

| Part no.     | Part name           | Thread    | Conduit<br>Ø<br>mm | Total<br>length<br>mm | Thread<br>length<br>mm | Outer Ø<br>mm | Inner Ø<br>mm |
|--------------|---------------------|-----------|--------------------|-----------------------|------------------------|---------------|---------------|
| <b>Black</b> |                     |           |                    |                       |                        |               |               |
| 6550 0475    | SILVYN® FLEXILOK PG | PG 9/1    | 13                 | 41                    | 10                     | 20            | 11,5          |
| 6550 0495    | SILVYN® FLEXILOK PG | PG 9/2    | 16                 | 42                    | 10                     | 23            | 11,5          |
| 6550 0485    | SILVYN® FLEXILOK PG | PG 11/1   | 13                 | 41                    | 10                     | 20            | 11,5          |
| 6550 0395    | SILVYN® FLEXILOK PG | PG 11/2   | 16                 | 42                    | 10                     | 23            | 14,5          |
| 6810 0055    | SILVYN® FLEXILOK PG | PG 13,5/1 | 16                 | 42                    | 10                     | 23            | 15,5          |
| 6810 0075    | SILVYN® FLEXILOK PG | PG 13,5/2 | 21                 | 45                    | 10                     | 29            | 16            |
| 6810 0065    | SILVYN® FLEXILOK PG | PG 16/1   | 16                 | 43                    | 11                     | 23            | 15,5          |
| 6810 0085    | SILVYN® FLEXILOK PG | PG 16/2   | 21                 | 46                    | 11                     | 29            | 17,5          |
| 6810 0095    | SILVYN® FLEXILOK PG | PG 21     | 28                 | 51                    | 12                     | 36            | 22,5          |
| 6888 0005    | SILVYN® FLEXILOK PG | PG 29     | 34                 | 54                    | 12                     | 43            | 30,5          |
| <b>Grey</b>  |                     |           |                    |                       |                        |               |               |
| 6550 0470    | SILVYN® FLEXILOK PG | PG 9/1    | 13                 | 41                    | 10                     | 20            | 11,5          |
| 6550 0490    | SILVYN® FLEXILOK PG | PG 9/2    | 16                 | 42                    | 10                     | 23            | 11,5          |
| 6550 0480    | SILVYN® FLEXILOK PG | PG 11/1   | 13                 | 41                    | 10                     | 20            | 11,5          |
| 6550 0390    | SILVYN® FLEXILOK PG | PG 11/2   | 16                 | 42                    | 10                     | 23            | 14,5          |
| 6810 0050    | SILVYN® FLEXILOK PG | PG 13,5/1 | 16                 | 42                    | 10                     | 23            | 15,5          |
| 6810 0070    | SILVYN® FLEXILOK PG | PG 13,5/2 | 21                 | 45                    | 10                     | 29            | 16            |
| 6810 0060    | SILVYN® FLEXILOK PG | PG 16/1   | 16                 | 43                    | 11                     | 23            | 15,5          |
| 6810 0080    | SILVYN® FLEXILOK PG | PG 16/2   | 21                 | 46                    | 11                     | 29            | 17,5          |
| 6810 0090    | SILVYN® FLEXILOK PG | PG 21     | 28                 | 51                    | 12                     | 36            | 22,5          |
| 6550 0620    | SILVYN® FLEXILOK PG | PG 29     | 34                 | 54                    | 12                     | 43            | 30,5          |

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

|   |                                       |             |
|---|---------------------------------------|-------------|
| Creator: M. Wegerer /PDP<br>Released: DAMU1/PDP | Document: DB65500475EN<br>Version: 01 | Page 1 of 1 |
|---|---------------------------------------|-------------|