


83260000	DATA SHEET	
Valid from: 17.09.2018	FLEXIMARK® Organized shrink tube	

FLEXIMARK® Organized Shrink tube



General Description:

- For single core and cable marking
- Can be printed with a thermal transfer printer as CAB A4+ / A4+M
- Recommended ribbon: 83260201- Ribbon FTI-Y 55-360 BK
- Also available as halogen-free and diesel-resistant version
- Is delivered in form of a roll

Technical data:

- Material: Polyolefin, shrinking ratio shrink tube: 3:1 (halogen-free variant: 2:1)
- Resistance: UV-resistant, resistant against fluids (SAE-AMS-DTL-23053 tested), Halogen-free variant: good chemical resistance, diesel-resistant version: additionally good resistance against diesel
- Colours: Yellow and white
- Temperature range: -55 °C up to +135 °C (Halogen-free: -30 °C up to +105 °C)
- Approvals: ROHS, UL 224

Elaborated by: PSM: S. Scheiter	Document: DB83260000EN Version: 01	Page 1 of 4
------------------------------------	---------------------------------------	-------------

83260000

DATA SHEET


Valid from:
17.09.2018

FLEXIMARK® Organized shrink tube

Article no.	Article designation	Length (mm)	Size before/ after shrink	Colour	Amount per row	Content (unit)
83260000	FLEXIMARK® Org. shrink. 2.4/0.8-50(1) WH	50.0	2.4/0,8	White	1	1000
83260001	FLEXIMARK® Org. shrink. 3.2/1.0-50(1) WH	50.0	3.2/1.0	White	1	1000
83260002	FLEXIMARK® Org. shrink. 4.8/1.6-50(1) WH	50.0	4.8/1.6	White	1	1000
83260003	FLEXIMARK® Org. shrink. 6.4/2.0-50(1) WH	50.0	6.4/2.0	White	1	1000
83260004	FLEXIMARK® Org. shrink. 9.5/3.0-50(1) WH	50.0	9.5/3.0	White	1	500
83260005	FLEXIMARK® Org. shrink. 12.7/4.0-50(1)WH	50.0	12.7/4.0	White	1	500
83260006	FLEXIMARK® Org. shrink.19.0/6.0-50(1)WH	50.0	19.0/6.0	White	1	500
83260007	FLEXIMARK® Org. shrink.25.4/8.0-50(1)WH	50.0	25.4/8.0	White	1	300
83260008	FLEXIMARK® Org. shrink38.1/12.7-75(1)WH	75.0	38.1/12.7	White	1	100
83260009	FLEXIMARK® Org. shrink. 2.4/0.8-38(1) WH	38.0	2.4/0.8	White	1	1000
83260010	FLEXIMARK® Org. shrink. 3.2/1.0-38(1) WH	38.0	3.2/1.0	White	1	1000
83260011	FLEXIMARK® Org. shrink. 4.8/1.6-38(1) WH	38.0	4.8/1.6	White	1	1000
83260012	FLEXIMARK® Org. shrink. 6.4/2.0-38(1) WH	38.0	6.4/2.0	White	1	1000
83260013	FLEXIMARK® Org. shrink. 9.5/3.0-38(1) WH	38.0	9.5/3.0	White	1	500
83260014	FLEXIMARK® Org. shrink.12.7/4.0-38(1)WH	38.0	12.7/4.0	White	1	500
83260015	FLEXIMARK® Org. shrink.19.0/6.0-38(1)WH	38.0	19.0/6.0	White	1	500
83260016	FLEXIMARK® Org. shrink.25.4/8.0-38(1)WH	38.0	25.4/8.0	White	1	300
83260017	FLEXIMARK® Org. shrink38.1/12.7-38(1)WH	38.0	38.1/12.7	White	1	100
83260018	FLEXIMARK® Org. shrink. 2.4/0.8-25(2) WH	25.0	2.4/0.8	White	2	2000
83260019	FLEXIMARK® Org. shrink. 3.2/1.0-25(2) WH	25.0	3.2/1.0	White	2	2000
83260020	FLEXIMARK® Org. shrink. 4.8/1.6-25(2) WH	25.0	4.8/1.6	White	2	2000
83260021	FLEXIMARK® Org. shrink. 6.4/2.0-25(2) WH	25.0	6.4/2.0	White	2	2000
83260022	FLEXIMARK® Org. shrink. 9.5/3.0-25(2) WH	25.0	9.5/3.0	White	2	1000
83260023	FLEXIMARK® Org. shrink. 4.8/1.6-25(2) WH	25.0	12.7/4.0	White	2	1000
83260024	FLEXIMARK® Org. shrink.19.0/6.0-25(2)WH	25.0	19.0/6.0	White	2	1000
83260025	FLEXIMARK® Org. shrink.25.4/8.0-25(2)WH	25.0	25.4/8.0	White	2	600
83260210	FLEXIMARK® Org. shrink. 4.8/1.6-25(2) WH	16.6	2.4/0.8	White	3	3000
83260211	FLEXIMARK® Org. shrink. 3.2/1.0-16.6(3) WH	16.6	3.2/1.0	White	3	3000
83260212	FLEXIMARK® Org. shrink. 3.2/1.0-16.6(3) WH	16.6	4.8/1.6	White	3	3000
83260207	FLEXIMARK® Org. shrink. 2.4/0.8-12.5(4) WH	12.5	2.4/0.8	White	4	4000
83260208	FLEXIMARK® Org. shrink. 3.2/1.0-12.5(4) WH	12.5	3.2/1.0	White	4	4000
83260209	FLEXIMARK® Org. shrink. 4.8/1.6-12.5(4) WH	12.5	4.8/1.6	White	4	4000
83260026	FLEXIMARK® Org. shrink. 2.4/0.8-50(1) YE	50.0	2.4/0.8	Yellow	1	1000
83260027	FLEXIMARK® Org. shrink. 3.2/1.0-50(1) YE	50.0	3.2/1.0	Yellow	1	1000
83260028	FLEXIMARK® Org. shrink. 4.8/1.6-50(1) YE	50.0	4.8/1.6	Yellow	1	1000
83260029	FLEXIMARK® Org. shrink. 6.4/2.0-50(1) YE	50.0	6.4/2.0	Yellow	1	1000
83260030	FLEXIMARK® Org. shrink. 9.5/3.0-50(1) YE	50.0	9.5/3.0	Yellow	1	500
83260031	FLEXIMARK® Org. shrink. 12.7/4.0-50(1)YE	50.0	12.7/4.0	Yellow	1	500
83260032	FLEXIMARK® Org. shrink.19.0/6.0-50(1)YE	50.0	19.0/6.0	Yellow	1	500
83260033	FLEXIMARK® Org. shrink.25.4/8.0-50(1)YE	50.0	25.4/8.0	Yellow	1	300
83260034	FLEXIMARK® Org. shrink 38.1/12.7-75(1)YE	75.0	38.1/12.7	Yellow	1	100
83260035	FLEXIMARK® Org. shrink.25.4/8.0-50(1)YE	38.0	2.4/0.8	Yellow	1	1000
83260036	FLEXIMARK® Org. shrink. 3.2/1.0-38(1) YE	38.0	3.2/1.0	Yellow	1	1000
83260037	FLEXIMARK® Org. shrink. 4.8/1.6-38(1) YE	38.0	4.8/1.6	Yellow	1	1000
83260038	FLEXIMARK® Org. shrink. 6.4/2.0-38(1) YE	38.0	6.4/2.0	Yellow	1	1000
83260039	FLEXIMARK® Org. shrink. 9.5/3.0-38(1) YE	38.0	9.5/3.0	Yellow	1	500
83260040	FLEXIMARK® Org. shrink.12.7/4.0-38(1)YE	38.0	12.7/4.0	Yellow	1	500
83260041	FLEXIMARK® Org. shrink.19.0/6.0-38(1)YE	38.0	9.0/6.0	Yellow	1	500
83260042	FLEXIMARK® Org. shrink.19.0/6.0-38(1)YE	38.0	25.4/8.0	Yellow	1	300
83260043	FLEXIMARK® Org. shrink38.1/12.7-38(1)YE	38.0	38.1/12.7	Yellow	1	100
83260044	FLEXIMARK® Org. shrink. 2.4/0.8-25(2) YE	25.0	2.4/0.8	Yellow	2	2000
83260045	FLEXIMARK® Org. shrink. 3.2/1.0-25(2) YE	25.0	3.2/1.0	Yellow	2	2000
83260046	FLEXIMARK® Org. shrink. 4.8/1.6-25(2) YE	25.0	4.8/1.6	Yellow	2	2000
83260047	FLEXIMARK® Org. shrink. 6.4/2.0-25(2) YE	25.0	6.4/2.0	Yellow	2	2000
83260048	FLEXIMARK® Org. shrink. 9.5/3.0-25(2) YE	25.0	9.5/3.0	Yellow	2	1000
83260049	FLEXIMARK® Org. shrink. 12.7/4.0-25(2)YE	25.0	12.7/4.0	Yellow	2	1000
83260216	FLEXIMARK® Org. shrink. 2.4/0.8-16.6(3) YE	16.6	2.4/0.8	Yellow	3	3000
83260217	FLEXIMARK® Org. shrink. 3.2/1.0-16.6(3) YE	16.6	3.2/1.0	Yellow	3	3000
83260218	FLEXIMARK® Org. shrink. 9.5/3.0-25(2) YE	16.6	4.8/1.6	Yellow	3	3000
83260213	FLEXIMARK® Org. shrink. 2.4/0.8-12.5(4) YE	12.5	2.4/0.8	Yellow	4	4000
83260214	FLEXIMARK® Org. shrink. 3.2/1.0-12.5(4) YE	12.5	3.2/1.0	Yellow	4	4000
83260215	FLEXIMARK® Org. shrink. 4.8/1.6-12.5(4) YE	12.5	4.8/1.6	Yellow	4	4000
83260051	FLEXIMARK® Org. shrink.25.4/8.0-25(2)YE	25.0	25.4/8.0	Yellow	2	600

Elaborated by:
PSM: S. ScheiterDocument: DB83260000EN
Version: 01


Page 2 of 4

83260000	DATA SHEET	
Valid from: 17.09.2018	FLEXIMARK® Organized shrink tube	

Organized Shrink tube halogen free

Article no.	Article designation	Length (mm)	Size before/ after shrinking	Colour	Amount per row	Content (unit)
83260052	FLEXIMARK® Org.shr 2.4/1.2-50(1) 0-hal WH	50	2,4/1.2	White	1	1000
83260053	FLEXIMARK® Org.shr 3.2/1.6-50(1) 0-hal WH	50	3.2/1.6	White	1	1000
83260054	FLEXIMARK® Org.shr 4.8/2.4-50(1) 0-hal WH	50	4.8/2.4	White	1	1000
83260055	FLEXIMARK® Org.shr 6.4/3.2-50(1) 0-hal WH	50	6.4/3.2	White	1	1000
83260056	FLEXIMARK® Org.shr 9.5/4.8-50(1) 0-hal WH	50	9.5/4.8	White	1	500
83260057	FLEXIMARK® Org.shr 12.7/6.4-50(1) 0-halWH	50	12.7/6.4	White	1	500
83260058	FLEXIMARK® Org.shr 19.1/9.5-50(1) 0-halWH	50	19.1/9.5	White	1	500
83260059	FLEXIMARK® Org.shr 25.4/12.7-50(1) 0-halWH	50	25.4/12.7	White	1	300
83260060	FLEXIMARK® Org.shr 38.1/19.1-50(1) 0-halWH	50	38.1/19.1	White	1	100
83260061	FLEXIMARK® Org.shr 50.8/25.4-50(1) 0-halWH	50	50.8/25.4	White	1	100
83260062	FLEXIMARK® Org.shr 2.4/1.2-38(1) 0-hal WH	38	2.4/1.2	White	1	1000
83260063	FLEXIMARK® Org.shr 3.2/1.6-38(1) 0-hal WH	38	3.2/1.6	White	1	1000
83260064	FLEXIMARK® Org.shr 4.8/2.4-38(1) 0-hal WH	38	4.8/2.4	White	1	1000
83260065	FLEXIMARK® Org.shr 6.4/3.2-38(1) 0-hal WH	38	6.4/3.2	White	1	1000
83260066	FLEXIMARK® Org.shr 9.5/4.8-38(1) 0-hal WH	38	9.5/4.8	White	1	500
83260067	FLEXIMARK® Org.shr 12.7/6.4-38(1) 0-halWH	38	12.7/6.4	White	1	500
83260068	FLEXIMARK® Org.shr 19.1/9.5-38(1) 0-halWH	38	19.1/9.5	White	1	500
83260069	FLEXIMARK® Org.shr 25.4/12.7-38(1) 0-halWH	38	25.4/12.7	White	1	300
83260070	FLEXIMARK® Org.shr 38.1/19.1-38(1) 0-halWH	38	38.1/19.1	White	1	100
83260071	FLEXIMARK® Org.shr 50.8/25.4-38(1) 0-halWH	38	50.8/25.4	White	1	100
83260072	FLEXIMARK® Org.shr 2.4/1.2-25(2) 0-hal WH	25	2.4/1.2	White	2	2000
83260073	FLEXIMARK® Org.shr 3.2/1.6-25(2) 0-hal WH	25	3.2/1.6	White	2	2000
83260074	FLEXIMARK® Org.shr 4.8/2.4-25(2) 0-hal WH	25	4.8/2.4	White	2	2000
83260075	FLEXIMARK® Org.shr 6.4/3.2-25(2) 0-hal WH	25	6.4/3.2	White	2	2000
83260076	FLEXIMARK® Org.shr 9.5/4.8-25(2) 0-hal WH	25	9.5/4.8	White	2	1000
83260077	FLEXIMARK® Org.shr 12.7/6.4-25(2) 0-hal WH	25	12.7/6.4	White	2	1000
83260078	FLEXIMARK® Org.shr 19.1/9.5-25(2) 0-hal WH	25	19.1/9.5	White	2	1000
83260079	FLEXIMARK® Org.shr 25.4/12.7-25(2) 0-halWH	25	25.4/12.7	White	2	600
83260080	FLEXIMARK® Org.shr 2.4/1.2-50(1) 0-hal YE	50	2.4/1.2	Yellow	1	1000
83260081	FLEXIMARK® Org.shr 3.2/1.6-50(1) 0-hal YE	50	3.2/1.6	Yellow	1	1000
83260082	FLEXIMARK® Org.shr 4.8/2.4-50(1) 0-hal YE	50	3.2/1.0	Yellow	1	1000
83260083	FLEXIMARK® Org.shr 6.4/3.2-50(1) 0-hal YE	50	6.4/3.2	Yellow	1	1000
83260084	FLEXIMARK® Org.shr 9.5/4.8-50(1) 0-hal YE	50	9.5/4.8	Yellow	1	500
83260085	FLEXIMARK® Org.shr 12.7/6.4-50(1)0-hal YE	50	12.7/6.4	Yellow	1	500
83260086	FLEXIMARK® Org.shr 19.1/9.5-50(1) 0-hal YE	50	19.1/9.5	Yellow	1	500
83260087	FLEXIMARK® Org.shr 25.4/12.7-50(1) 0-halYE	50	25.4/12.7	Yellow	1	300
83260088	FLEXIMARK® Org.shr 38.1/19.1-50(1) 0-halYE	50	38.1/19.1	Yellow	1	100
83260089	FLEXIMARK® Org.shr 50.8/25.4-50(1) 0-halYE	50	50.8/25.4	Yellow	1	100
83260090	FLEXIMARK® Org.shr 2.4/1.2-38(1) 0-hal YE	38	2.4/1.2	Yellow	1	1000
83260091	FLEXIMARK® Org.shr 3.2/1.6-38(1) 0-hal YE	38	3.2/1.6	Yellow	1	1000
83260092	FLEXIMARK® Org.shr 4.8/2.4-38(1) 0-hal YE	38	4.8/2.4	Yellow	1	1000
83260093	FLEXIMARK® Org.shr 6.4/3.2-38(1) 0-hal YE	38	6.4/3.2	Yellow	1	1000
83260094	FLEXIMARK® Org.shr 9.5/4.8-38(1) 0-hal YE	38	9.5/4.8	Yellow	1	500
83260095	FLEXIMARK® Org.shr 12.7/6.4-38(1) 0-hal YE	38	12.7/6.4	Yellow	1	500
83260096	FLEXIMARK® Org.shr 19.1/9.5-38(1) 0-hal YE	38	19.1/9.5	Yellow	1	500
83260097	FLEXIMARK® Org.shr 25.4/12.7-38(1) 0-halYE	38	25.4/12.7	Yellow	1	300
83260098	FLEXIMARK® Org.shr 38.1/19.1-38(1) 0-halYE	38	38.1/19.1	Yellow	1	100
83260099	FLEXIMARK® Org.shr 50.8/25.4-38(1) 0-halYE	38	50.8/25.4	Yellow	1	100
83260100	FLEXIMARK® Org.shr 2.4/1.2-25(2) 0-hal YE	25	2.4/1.2	Yellow	2	2000
83260101	FLEXIMARK® Org.shr 3.2/1.6-25(2) 0-hal YE	25	3.2/1.6	Yellow	2	2000
83260102	FLEXIMARK® Org.shr 4.8/2.4-25(2) 0-hal YE	25	4.8/2.4	Yellow	2	2000
83260103	FLEXIMARK® Org.shr 6.4/3.2-25(2) 0-hal YE	25	6.4/3.2	Yellow	2	2000
83260104	FLEXIMARK® Org.shr 9.5/4.8-25(2) 0-hal YE	25	9.5/4.8	Yellow	2	1000
83260105	FLEXIMARK® Org.shr 12.7/6.4-25(2)0-hal YE	25	12.7/6.4	Yellow	2	1000
83260106	FLEXIMARK® Org.shr 19.1/9.5-25(2) 0-hal YE	25	19.1/9.5	Yellow	2	1000
83260107	FLEXIMARK® Org.shr 25.4/12.7-25(2) 0-halYE	25	25.4/12.7	Yellow	2	600

Elaborated by: PSM: S. Scheiter	Document: DB83260000EN Version: 01	Page 3 of 4
------------------------------------	---------------------------------------	-------------

83260000	DATA SHEET	
Valid from: 17.09.2018	FLEXIMARK® Organized shrink tube	

Organized Shrink tube diesel resistant

Article no.	Article designation	Length(mm)	Size before/ after shrinking	Colour	Amount per row	Content (unit)
83260108	FLEXIMARK® Org.shr 2.4/0.8-50(1) DR WH	50	2.4/0.8	White	1	1000
83260109	FLEXIMARK® Org.shr 3.2/1.1-50(1) DR WH	50	3.2/1.1	White	1	1000
83260110	FLEXIMARK® Org.shr 4.8/1.6-50(1) DR WH	50	4.8/1.6	White	1	1000
83260111	FLEXIMARK® Org.shr 6.4/3.2-50(1) O-hal WH	50	6.4/3.2	White	1	1000
83260112	FLEXIMARK® Org.shr 9.5/3.2-50(1) DR WH	50	9.5/3.2	White	1	500
83260113	FLEXIMARK® Org.shr 12.7/4.2-50(1) DR WH	50	12.7/4.2	White	1	500
83260114	FLEXIMARK® Org.shr 19.1/6.4-50(1) DR WH	50	19.1/6.4	White	1	500
83260115	FLEXIMARK® Org.shr 25.4/9.5-50(1)DR WH	50	25.4/9.5	White	1	300
83260116	FLEXIMARK® Org.shr 38.1/12.7-50(1)DR WH	50	38.1/12.7	White	1	100
83260117	FLEXIMARK® Org.shr 38.1/12.7-75(1)DR WH	75	38.1/12.7	White	1	100
83260118	FLEXIMARK® Org.shr 2.4/0.8-38(1) DR WH	38	2.4/0.8	White	1	1000
83260119	FLEXIMARK® Org.shr 3.2/1.1-38(1) DR WH	38	3.2/1.1	White	1	1000
83260120	FLEXIMARK® Org.shr 4.8/1.6-38(1) DR WH	38	4.8/1.6	White	1	1000
83260121	FLEXIMARK® Org.shr 6.4/2.1-38(1) DR WH	38	6.4/2.1	White	1	1000
83260122	FLEXIMARK® Org.shr 9.5/3.2-38(1) DR WH	38	9.5/3.2	White	1	1000
83260123	FLEXIMARK® Org.shr 12.7/4.2-38(1) DR WH	38	12.7/4.2	White	1	500
83260124	FLEXIMARK® Org.shr 19.1/6.4-38(1) DR WH	38	19.1/6.4	White	1	500
83260125	FLEXIMARK® Org.shr 25.4/9.5-38(1) DR WH	38	25.4/9.5	White	1	300
83260126	FLEXIMARK® Org.shr 38.1/12.7-38(1) DR WH	38	38.1/12.7	White	1	100
83260127	FLEXIMARK® Org.shr 2.4/0.8-25(2) DR WH	25	2.4/0.8	White	1	100
83260128	FLEXIMARK® Org.shr 3.2/1.1-25(2) DR WH	25	3.2/1.1	White	2	2000
83260129	FLEXIMARK® Org.shr 4.8/1.6-25(2) DR WH	25	4.8/1.6	White	2	2000
83260130	FLEXIMARK® Org.shr 6.4/2.1-25(2) DR WH	25	6.4/2.1	White	2	2000
83260131	FLEXIMARK® Org.shr 9.5/3.2-25(2) DR WH	25	9.5/3.2	White	2	1000
83260132	FLEXIMARK® Org.shr 12.7/4.2-25(2) DR WH	25	12.7/4.2	White	2	1000
83260133	FLEXIMARK® Org.shr 19.1/6.4-25(2) DR WH	25	19.1/6.4	White	2	1000
83260134	FLEXIMARK® Org.shr 25.4/9.5-25(2) DR WH	25	25.4/9.5	White	2	600
83260135	FLEXIMARK® Org.shr 38.1/12.7-25(2) DR WH	25	38.1/12.7	White	2	200
83260136	FLEXIMARK® Org.shr 2.4/0.8-50(1) DR YE	50	2.4/0.8	Yellow	1	1000
83260137	FLEXIMARK® Org.shr 3.2/1.1-50(1) DR YE	50	3.2/1.1	Yellow	1	1000
83260138	FLEXIMARK® Org.shr 4.8/1.6-50(1) DR YE	50	4.8/1.6	Yellow	1	1000
83260139	FLEXIMARK® Org.shr 6.4/2.1-50(1) DR YE	50	6.4/2.1	Yellow	1	1000
83260140	FLEXIMARK® Org.shr 9.5/3.2-50(1) DR YE	50	9.5/3.2	Yellow	1	500
83260141	FLEXIMARK® Org.shr 12.7/4.2-50(1) DR YE	50	12.7/4.2	Yellow	1	500
83260142	FLEXIMARK® Org.shr 19.1/6.4-50(1) DR YE	50	19.1/6.4	Yellow	1	500
83260143	FLEXIMARK® Org.shr 25.4/9.5-50(1) DR YE	50	25.4/9.5	Yellow	1	300
83260144	FLEXIMARK® Org.shr 38.1/12.7-50(1)DR YE	50	38.1/12.7	Yellow	1	100
83260145	FLEXIMARK® Org.shr 38.1/12.7-75(1)DR YE	75	38.1/12.7	Yellow	1	100
83260146	FLEXIMARK® Org.shr 2.4/0.8-38(1) DR YE	38	2.4/0.8	Yellow	1	1000
83260147	FLEXIMARK® Org.shr 3.2/1.1-38(1) DR YE	38	3.2/1.1	Yellow	1	1000
83260148	FLEXIMARK® Org.shr 4.8/1.6-38(1) DR YE	38	4.8/1.6	Yellow	1	1000
83260149	FLEXIMARK® Org.shr 6.4/2.1-38(1) DR YE	38	6.4/2.1	Yellow	1	1000
83260150	FLEXIMARK® Org.shr 9.5/3.2-38(1) DR YE	38	9.5/3.2	Yellow	1	500
83260151	FLEXIMARK® Org.shr 12.7/4.2-38(1) DR YE	38	12.7/4.2	Yellow	1	500
83260152	FLEXIMARK® Org.shr 19.1/6.4-38(1) DR YE	38	19.1/6.4	Yellow	1	500
83260153	FLEXIMARK® Org.shr 25.4/9.5-38(1) DR YE	38	25.4/9.5	Yellow	1	300
83260154	FLEXIMARK® Org.shr 38.1/12.7-38(1) DR YE	38	38.1/12.7	Yellow	1	100
83260155	FLEXIMARK® Org.shr 2.4/0.8-25(2) DR YE	25	2.4/0.8	Yellow	2	2000
83260156	FLEXIMARK® Org.shr 3.2/1.1-25(2) DR YE	25	3.2/1.1	Yellow	2	2000
83260157	FLEXIMARK® Org.shr 4.8/1.6-25(2) DR YE	25	4.8/1.6	Yellow	2	2000
83260158	FLEXIMARK® Org.shr 6.4/2.1-25(2) DR YE	25	6.4/2.1	Yellow	2	2000
83260159	FLEXIMARK® Org.shr 9.5/3.2-25(2) DR YE	25	9.5/3.2	Yellow	2	1000
83260160	FLEXIMARK® Org.shr 12.7/4.2-25(2) DR YE	25	12.7/4.2	Yellow	2	1000
83260161	FLEXIMARK® Org.shr 19.1/6.4-25(2) DR YE	25	19.1/6.4	Yellow	2	1000
83260162	FLEXIMARK® Org.shr 25.4/9.5-25(2) DR YE	25	25.4/9.5	Yellow	2	600
83260163	FLEXIMARK® Org.shr 38.1/12.7-25(2) DR YE	25	38.1/12.7	Yellow	2	200

Foot note:

Photographs are not to scale and do not represent detailed images of the respective products.

Elaborated by: PSM: S. Scheiter	Document: DB83260000EN Version: 01	Page 4 of 4
------------------------------------	---------------------------------------	-------------