


44422022	DATA SHEET	
Valid from: 29.08.2022	EPIC® H-B 32 TG 2x	

Description

- The large, robust housing for two inserts of size 16



General Characteristics

Series	H-B 32
Version	Hood
Locking	Bolts for double lever
Cable entry	2x straight, see table
Gland body	See table
Protection (DIN EN 60529)	IP 65 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C

Materials / Surfaces

Housing	Aluminium alloy, powder-coated, grey
Locking	Steel, zinc-plated
Gland body	Brass, nickel plated


Standard

Safety Standard	IEC 61984
-----------------	-----------


Versions

Article number	Article description	Cable entry	Gland body
44422022	EPIC® H-B 32 TG 2xM25	M25	No
44422023	EPIC® H-B 32 TG 2xM32	M32	No

Creator: BEGE1/PDP Released: IVSE1/PDP	Document: DB44422022EN Version: 00	Page 1 of 2
---	---------------------------------------	-------------

44422022	DATA SHEET	
Valid from: 29.08.2022	EPIC® H-B 32 TG 2x	

Technical Drawings



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Application range

Plant engineering, Control engineering, Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP Released: IVSE1/PDP	Document: DB44422022EN Version: 00	Page 2 of 2
---	---------------------------------------	-------------