


0163023	DATA SHEET	
Valid from: 01.04.2019	IEC compensating cable KP 15 L-SIL-S 2x1,5 round	

Application

The compensating cable KP 15 L-SIL-S 2 x 1,5 mm² is a silicone insulated cable which transmits the thermoelectric voltage of PtRh/Pt thermocouples. It is for flexible use and fixed installation in dry rooms with low mechanical load. They may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range. The steel wire armoring serves as mechanical protection.

Design

Conductor	1.5 mm ² (48 x 0.20 mm)	
Conductor material	RCB/SCB alloying, accuracy class 2 according IEC 60584	
	Positive conductor:	Cu (copper)
	Negative conductor:	CuNi (cupronickel)
Core insulation	Silicone compound	
Core identification	Positive conductor:	orange
	Negative conductor:	white
Core layering	Cores twisted together	
Outer sheath	Silicone compound, colour:	orange
Armouring	Galvanized steel wire braiding with interweaved, orange identification thread	

Electrical properties

Limiting deviation class 2	±60 µV (±5.0 °C) / measuring point temperature +1000 °C
----------------------------	---

Mechanical and thermal properties

Temperature range	occasional flexing:	-25 °C up to +180 °C
Minimum bending radius	occasional flexing:	15 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2	

Creator: TOME/PCM Released: ALTE/PDC	Document: DB0163023EN Version: 02	Page 1 of 1
---	--------------------------------------	-------------