


52107800	<b>DATA SHEET</b>	
Valid from: 26.03.2021	<b>SKINDICHT® RWV-M / RWV-M O. E+D</b>	

The SKINDICHT® RWV-M is a zinc die-cast cable gland with 90° elbow. The locknut enables the angle gland to be installed in any position.



### Component parts:

Angular housing	Zinc die-casting, nickel-plated
Pressure screw (Only exist in the version SKINDICHT RWV-M)	Brass, nickel-plated
Locknut	Brass, nickel-plated
Pressure washers (Only exist in the version SKINDICHT RWV-M)	Steel, zinc-plated
Incised sealing ring (Only exist in the version SKINDICHT RWV-M)	CR
O-ring	NBR


### Technical features:

Connecting thread	M12x1,5 up to M40x1,5 acc. to EN 60423
Temperature range	-20 °C up to +100 °C
Protection class (Does not apply to version SKINDICHT RWV-M O. E+D)	IP55 test acc. to EN 60529


### Norm references:



Creator: T. Dvoulety /PDP Released: DAMU1/PDP	Document: DB52107800EN Version: 08	Page 1 of 3
--	---------------------------------------	-------------


52107800	<b>DATA SHEET</b>	
Valid from: 26.03.2021	<b>SKINDICHT® RWV-M / RWV-M O. E+D</b>	

### SKINDICHT® RWV-M



M	SW1 [mm]	SW3 [mm]	SW2 [mm]	Ø A1 [mm]	Ø A3 [mm]	C [mm]	D [mm]	Ø F [mm] incised sealing ring	Ø G [mm]	L [mm]	O-Ring [mm]	Article No.
M12x1,5	14	12	17	16	18,9	26,1	6,5	5	8	20,5	11x2,5	52107800
M16x1,5	18	16	22	20	24,5	28,6	6,5	3/6/9	12	23,5	15x2,5	52107810
M20x1,5	22	20	27	24	30,1	35,1	7,5	4/7/10/13	15	28,5	19x2,5	52107820
M25x1,5	27	25	32	29	35,7	38,1	8,5	8,5/11,5/14,5/17,5	20	31,0	24x2,5	52107830
M32x1,5	34	32	41	36	45,6	44,6	8,5	16/19/22/25	27	33,5	30x2,5	52107840
M40x1,5	42	40	46	45	50,6	53,1	10,5	23/26/29/32	35	43,0	38x2,5	52107850

### SKINDICHT® RWV-M O. E+D



M	SW1 [mm]	SW2 [mm]	Ø A1 [mm]	Ø A2 [mm]	B [mm]	D [mm]	Ø G [mm]	L [mm]	O-Ring [mm]	Article No.
M12x1,5	14	17	16	18,9	21,0	6,5	8	20,5	11x2,5	52107801
M16x1,5	18	22	20	24,5	23,0	6,5	12	23,5	15x2,5	52107811
M20x1,5	22	27	24	30,1	28,5	7,5	15	28,5	19x2,5	52107821
M25x1,5	27	32	29	35,7	30,0	8,5	20	31,0	24x2,5	52107831
M32x1,5	34	41	36	45,6	36,5	8,5	27	33,5	30x2,5	52107841
M40x1,5	42	46	45	50,6	43,0	10,5	35	43,0	38x2,5	52107851

52107800	<b>DATA SHEET</b>	
Valid from: 26.03.2021	<b>SKINDICHT® RWV-M / RWV-M O. E+D</b>	

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: T. Dvoulety /PDP Released: DAMU1/PDP	Document: DB52107800EN Version: 08	Page 3 of 3
--	---------------------------------------	-------------