

61760060	DATA SHEET
Valid from: 26.05.2021	Insulating Tube ISS

Insulation tube made of silicone for bundling and insulating cables against heat and cold

Excellent mechanical, electrical and chemical properties

- Good UV resistance
- Highly flexible



Material: Silicone

Technical Features:

Inner Diameter 2 up to 10mm
 Temperature range -60°C up to +220°C

Additional features:

Fire classification HB acc. to UL94
 Breakdown voltage 18kV/mm
 High Flexible
 UV-Resistant

ETIM 5.0 Class-ID: EC002254
 ETIM 5.0 Class-Description: Cable insulation hose

Colour: natural

Reference standards: IEC 60684,3-121 up to 124

Article List:

Art. No.	Article designation	Internal diameter mm	Wall thickness mm	PU
61760060	ISS 2	2	0,4	100m
61760070	ISS 3	3	0,4	100m
61760080	ISS 4	4	0,75	100m
61760090	ISS 5	5	0,9	100m
61760100	ISS 6	6	0,9	100m
61760110	ISS 7	7	0,9	100m
61760120	ISS 8	8	1	100m
61760130	ISS 9	9	1,05	100m
61760140	ISS 10	10	1,05	100m

Foot note:

The photographs are not to scale and are not detailed illustrations of the respective products.