

44429334	DATA SHEET	
Valid from: 17.09.2018	EPIC® LS1.5 MALE CONTACTS SCEM	

Description

- Male contacts for LS 1.5 circular connectors



Article Number	Article	Version	For design
3,6 mm male contacts			
44429334	LS1.5 A SCEM 3,6MM AU 0,75-1,5	3,6 mm male 0,75-1,5	for type A1, A3
44429335	LS1.5 A SCEM 3,6MM AU 1,0-2,5	3,6 mm male 1,0-2,5mm ²	for type A1, A3
44429336	LS1.5 A SCEM 3,6MM AU 1,5-4,0	3,6 mm male 1,5-4,0mm ²	for type A1, A3
44429337	LS1.5 A SCEM 3,6MM AU 4,0-6,0	3,6 mm male 4,0-6,0mm ²	for type A1, A3
44429338	LS1.5 A SCEM 3,6MM AU 6,0-10,0	3,6 mm male 6,0-10,0mm ²	for type A1, A3
44429326	LS1.5 F SCEM 3,6MM AU 1,0-2,5	3,6 mm male 1,0-2,5mm ²	for type F6
44429327	LS1.5 F SCEM 3,6MM AU 2,5-4,0	3,6 mm male 2,5-4,0mm ²	for type F6
44429328	LS1.5 F SCEM 3,6MM AU 4,0-6,0	3,6 mm male 4,0-6,0mm ²	for type F6
44429329	LS1.5 F SCEM 3,6MM AU 6,0-16,0	3,6 mm male 6,0-16,0mm ²	for type F6
2 mm male contacts			
44429339	LS1.5 A SCEM 2MM AU 0,14-0,25	2 mm male 0,14-0,25mm ²	for type A1, A3
44429340	LS1.5 A SCEM 2MM AU 0,25-1,0	2 mm male 0,25-1,0mm ²	for type A1, A3
44429341	LS1.5 A SCEM 2MM AU 0,75-1,5	2 mm male 0,75-1,5mm ²	for type A1, A3
44429342	LS1.5 A SCEM 2MM AU 1,0-2,5	2 mm male 1,0-2,5mm ²	for type A1, A3
44429343	LS1.5 A SCEM 2MM AU 4,0	2 mm male 2,5-4,0mm ²	for type A1, A3
44429330	LS1.5 F SCEM 2MM AU 0,25-1,0	2 mm male 0,25-1,0mm ²	for type F6
44429331	LS1.5 F SCEM 2MM AU 0,75-1,5	2 mm male 0,75-1,5mm ²	for type F6
44429332	LS1.5 F SCEM 2MM AU 1,0-2,5	2 mm male 1,0-2,5mm ²	for type F6
44429333	LS1.5 F SCEM 2MM AU 2,5-4,0	2 mm male 2,5-4,0mm ²	for type F6



Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB44429334EN Version: 01	Page 1 of 1
---	---------------------------------------	-------------