| Valid from: | |
|-------------|--|
| 07.12.2018 | |

DATA SHEET FLEXIMARK[®] Cablelabel LFL

Cable label for cable marking. Mounting with cable tie. Delivered on perforated sheets designed for laser printing. UVresistant.

Technical data:

Material: Operating temperature: Sheet size: Colour: Recommended storage:

Mounting:

One or two cable ties.


Other product data:

ETIM Classification: EC001288

Advantages:

Supplied as punched and perforated A5 and A4 sheets. Printed in standard office laser printers, both sides are printable. The label has pre punched holes for one or two cable ties.

| Creator: Fleximark/LR | Document: DB83254750EN Version: 00 | Page 1 of 3 |
|-----------------------|---------------------------------------|-------------|
|-----------------------|---------------------------------------|-------------|







Product data:

| E-nr. | LAPP Part no. | Article designation | Size/ Label WxH mm | Content/ unit | colour | Content (Unit) | PU |
|---------|------------------|----------------------------|-----------------------|------------------|--------|-------------------|----|
| 2972058 | 83254750 | LFL 2H 9.9x26 YE/WH | 9.9x26 | 40 | Yellow | 10 | 1 |
| 2972059 | 83254760 | LFL 1H 9.9x35 YE/WH | 9,9x35 | 40 | Yellow | 10 | 1 |
| 2972097 | 83254765 | Cablelabel 9.9-66 YE/WH A4 | 9,9-66 | 56 | Yellow | 10 | 1 |

Resistance of FLEXIMARK® Cablelabel LFL:

RICE test SP-2171

| | Resista | nce test | | Chemical resistance test with abrasion | | | | | |
|----------------|-------------------------|-------------------------|-----------------------------|--|---|----------------------|-------------------------|-----------------------------------|-----------------------------|
| FLEXIMARK® | UV | Ageing | Diesel | Acid (H₂SO₄) 25% | Alkali (Detergent solution, 10%) | Distilled water | Salt water (5% NACI) | Transformer oil (Nytro 10X) | Ethanol |
| Cablelabel LFL | Tested & Recommended | Tested & Recommended | Tested & not recommended | Tested & not recommended | Tested & recommended | Tested & recommended | Tested & recommended | Tested & recommended | Tested & not recommended |

| Creator: Fleximark/LR | Document: DB83254750EN Version: 00 | Page 2 of 3 |
|-----------------------|---------------------------------------|-------------|
|-----------------------|---------------------------------------|-------------|


DATA SHEET




FLEXIMARK[®] Cablelabel LFL

Related products

FLEXIMARK[®] Cablelabel LFL can be printed using FLEXIMARK[®] Software and an office laser printer. Select label in the label selector in the program, add to the table what to print, select printer and print.



Easily mounted with plastic cable ties (available in our range).



Note:

Pictures are not to scale and do not represent detailed images of each product.

| Version: 00 | Creator: Fleximark/LR | Document: DB83254750EN Version: 00 | Page 3 of 3 |
|-------------|-----------------------|---------------------------------------|-------------|
|-------------|-----------------------|---------------------------------------|-------------|