


| | | |
|---------------------------|----------------------------|---|
| 10563000 | DATA SHEET |  |
| Valid from: 17.09.2018 | EPIC® H-A 16 TBF-LB | |

Description

- These connectors are attractive because of their compact housing.
- Small and compact for applications with high number of contacts



General characteristics

| | |
|------------------------------|--|
| Series | H-A 16 |
| Version | Cable coupler hood |
| Locking | single lever |
| Cable entry, direction | straight |
| Cable entry, thread | PG 16 |
| Gland body installed | yes |
| Protection (DIN EN 60529) | IP 65 (latched) |
| Protection (NEMA 250, UL50E) | 4, 12 (latched) |
| Temperature range | -40°C to +100°C, short-term up to +125°C |

Materials and surfaces

| | |
|------------|--------------------------------------|
| Housing | Aluminium alloy, powder-coated, grey |
| Gland body | Brass, nickel-plated |
| Lever | Steel, zinc-plated |
| Gasket | NBR |

Approvals

| | |
|----------------------------|------|
| VDE-Approval, VDE-REG.-Nr. | B437 |
|----------------------------|------|



Standards

| | |
|-----------------|-----------|
| Safety Standard | IEC 61984 |
|-----------------|-----------|

| | | |
|---|---------------------------------------|-------------|
| Creator: MANA2/PDP Released: IVSE1/PDP | Document: DB10563000EN Version: 01 | Page 1 of 2 |
|---|---------------------------------------|-------------|

| | | |
|---------------------------|---------------------|---|
| 10563000 | DATA SHEET |  |
| Valid from: 17.09.2018 | EPIC® H-A 16 TBF-LB | |

Drawings



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Compact, robust metal housings size H-A 16

Application range

Machine and equipment manufacturing
Control engineering
Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

| | | |
|---|---------------------------------------|-------------|
| Creator: MANA2/PDP Released: IVSE1/PDP | Document: DB10563000EN Version: 01 | Page 2 of 2 |
|---|---------------------------------------|-------------|