

0025319	DATA SHEET	
Valid from: 23.08.2018	ÖLFLEX® SERVO FD 796 P	

Application

ÖLFLEX® SERVO FD 796 P cables are high-flexible, oil-resistant, halogen free, low capacitance servo motor cables with an outer sheath of Polyurethane for the European, North American and Canadian market.

They are designed for use in high-dynamic applications with acceleration up to 50 m/s² in power chains as well as for fixed installation subject to medium mechanical load conditions.

They are also suitable for use in dry, damp or wet areas. They are suitable for outdoor use if the indicated temperature range is observed.

ÖLFLEX® SERVO FD 796 P cables are increased resistant to oils and at room temperature largely resistant to acids and alkalis. The outer sheath withstands high mechanical stresses, in particular abrasion and dragging. It is also cut proof and resists microbes and hydrolysis.

They are especially suitable for increased requirements (Extended Line) in power chains and in permanently moved machine parts. They are suitable for linear, automated movements. The maximum tensile load is 15 N/mm² of conductor cross-section during installation and operation. Compulsory guidance is not permitted. The control pairs are shielded.

Application range:

Power drive systems in automation engineering, connecting cable between servo controller and motor, in power chains or moving machine parts, for use in assembling- & pick-and -place machines, machine tools and transfer lines.

Use acc. to UL: PUR sheathed cable for external interconnection of electronic equipment.

Use acc. to cRUus: PUR sheathed cable for external interconnection of electronic equipment with or without mechanical load conditions.

Use acc. to CSA: PUR sheathed cable for external interconnection without mechanical load conditions.

Design

Design	according to UL AWM Style 20234 and based on EN 50525-2-21 resp. VDE 0285-2-21
Approvals	UL AWM 758, Style 20234 (File No. E63634) cRUus AWM I A/B II A/B (File No. E63634) CSA AWM I/II A ◁ VDE-REG 8591 ▷ (≥ 1.5 mm ²)
Conductor	extra fine wire strands of bare copper acc. to IEC 60228 resp. VDE 0295, Class 6
Core insulation	Polypropylen- based compound
Core identification	power conductors: black with white alphanumeric labelling U/L1/C/L+; V/L2; W/L3/D/L-; GN/YE ground conductor signal pairs: with 1pair: WH; BK with 2 pairs: 0.34 mm ² : WH; BN; GN; YE, ≥ 0.75mm ² : BK with WH numbers 5-8 acc. to VDE 0293-334 signal pairs with different conductor cross-section: 1 mm ² : BK with WH numbers 5-6 1.5 mm ² : BK with WH numbers 7-8
Pair shield	signal pairs: with 1 pair: Braid of tinned copper wires, coverage = 85% (nominal value) with 2 pairs: Aluminium-laminated foil, drain wire, braid of tinned copper wires, coverage = 85% (nominal value)
Cable make-up	4 power conductors (optionally with 1 resp. 2 signal pairs) stranded together with filler cords
Outer sheath	Polyurethane-compound TPU acc. to EN 50363-10-2 resp. VDE 0207-363-10-2 UL AWM 758, CSA AWM C22.2 No.210-15 colour: Black, similar RAL 9005

Creator: LABU/PDC Released: ALTE/PDC	Document: DB0025319EN Version: 06	Page 1 of 3
---	--------------------------------------	-------------

We reserve all rights according to DIN ISO 16016.

PD 0019/05_04.18EN

0025319	DATA SHEET	
Valid from: 23.08.2018	ÖLFLEX® SERVO FD 796 P	

Electrical properties

Nominal voltage	VDE U ₀ / U:	600/1000 V
	UL/CSA:	1000 V
Test voltage	core / core:	4000 V AC
	core / screen:	4000 V AC

Mechanical and thermal properties

Min. bending radius	flexing:	up from 7.5 x cable diameter
	fixed installation:	4 x cable diameter
Temperature range	flexing (VDE):	-40 °C up to +90 °C max. conductor temp.
	flexing (UL/CSA):	up to +80 °C max. conductor temp.
	fixed installation (VDE):	-50 °C up to +90 °C max. conductor temp.
	fixed installation(UL/CSA):	up to +80 °C max. conductor temp.
Flammability	flame retardant in acc. with IEC 60332-1-2 resp. VDE 0482-332-1-2	
	UL: Vertical flame test VW-1	
	CSA: FT1	
Halogen-free	acc. to VDE 0472 part 815	
UV-resistance	acc. to EN 50618 (VDE 0283-618)	
	EN 50620 (VDE 0285-620)	
	EN ISO 4892-2-2013, method A (change of colour allowed)	
Oil resistance	acc. to EN 50363-10-2 resp. VDE 0207-363-10-2	
MUD resistance	MUD resistant acc. to IEC 61892-4 Annex D	
Tests	acc. to IEC 60811 resp. VDE 0473 part 811, VDE 0472, EN 50395, EN 50396, UL 1581 and CSA C22.2	
EU Directives	These cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive)	

Dynamic performance

Pulling force (Dynamic):	≤ 20 N/mm ²
Pulling force (Static):	≤ 50 N/mm ²
Max. Acceleration:	see Table A
Max. Speed (sliding):	5 m/s resp. 300 m/min
Max. Length (horizontal):	see Table A and B (typically 50 m, max. 100 m)
Bending cycles and power chain operation parameters	See Selection Table A2-1 in the appendix of our online catalogue For use in power chains: Please comply with assembly guideline Appendix T3
Max. Torsion load:	+/- 30° /m


Creator: LABU/PDC	Document: DB0025319EN	Page 2 of 3
Released: ALTE/PDC	Version: 06	

We reserve all rights according to DIN ISO 16016.

PD 0019/05_04.18EN

0025319	DATA SHEET	
Valid from: 23.08.2018	ÖLFLEX® SERVO FD 796 P	

Table A $\leq 16 \text{ mm}^2$



Travel length	Acceleration
[m]	[m / sec ²]
0	50
3	50
5	30
10	15
15	8
20	5
25	4
30	3
35	2
40	2
45	2
50	1.5
100	1.0