DATA SHEET

valid from: 01.01.2019

0046900

ÖLFLEX® HEAT 180 H05SS-F EWKF



Application

ÖLFLEX® HEAT 180 H05SS-F EWKF are silicone cables designed for use as power and control cables at high ambient temperatures. The use of these cables is recommended for example in the following fields: Steel and iron works, cement and ceramic works, foundries, bakery equipment, electric motor industry, sauna and solarium construction, thermal and heating elements, lighting technology, ventilator engineering, air conditioning technology, oven construction, galvanization technology and polymer processing.

The product is certified by a member of CENELEC and is marked with ⊲HAR⊳.

Design

Design nach EN 50525-2-83 bzw. VDE 0285-525-2-83

Certification H05SS-F acc. to EN 50525-2-83 resp. VDE 0285-525-2-83

Conductor fine wire strand of tinned copper acc.to IEC 60228 resp. VDE 0295, class 5

Insulation silicone compound EI2 acc. to VDE 0207-363-1, EWKF-quality

starting at 3 cores with GN/YE ground conductor

up to 5 cores coloured acc. to VDE 0293-308

Stranding cores are stranded in layers

Outer sheath silicone compound EM9 acc. to VDE 0207-363-2-1, EWKF-quality

colour: black, similar RAL 9005

Electrical properties at 20°C

Core identification code

Specific volume resistivity $> 200 \; G\Omega \; x \; cm$ Rated voltage $U_0/U: 300/500 \; V$ Test voltage $2000 \; V \; AC$

Mechanical and thermal properties

Minimum bending radius occasional flexing: 15 x outer diameter

fixed installation: 4 x outer diameter

Temperature range occasional flexing: -50 °C bis +180 °C

fixed installation: -50°C bis +180°C

Flammability flame retardant in acc. with IEC 60332-1-2 resp. VDE 0482-332-1-2

Halogen free acc. to IEC 60754-1 Corrosivity of gases acc. to IEC 60754-2

General requirements These cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive)