0012752 DATA SHEET

valid from: O1.01.2019 ÖLFLEX® 540 CP



Application

ÖLFLEX® 540 CP cables are highly flexible oil-resistant connecting cables with a core insulation of TPE and an outer sheath of Polyurethane for flexible use and fixed installation under increased mechanical load conditions. They are also suitable for use in dry, damp or wet areas. They are suitable for outdoor use if the indicated temperature range is observed. They are suitable for constant use in fresh water to a depth of 10 m and at a maximum water temperature of 40°C according to EN 50565-2. They are suitable for occasional, non-automated movements. The maximum tensile load is 15 N/mm² of conductor cross-section during installation and operation. Compulsory guidance is not permitted.

ÖLFLEX® 540 CP cables are increased resistant to oils and at room temperature largely resistant to acids and alkalis.

The outer sheath withstands high mechanical stresses, in particular abrasion and dragging. It is also cut proof and resists microbes and hydrolysis. All materials used are halogen-free. The screening braid protects against interference from electrical fields.

Application range: Agricultural equipment, power tools like drill machines, circular hand saw, portable motors, construction machinery, machine tools and submersible pumps.

Design

Test voltage

Design based on standard

EN 50525-2-21 bzw. VDE 0285-525-2-21 EN 50525-2-51 bzw. VDE 0285-525-2-51

Certification up to 1,0 mm²: \triangleleft VDE-REG 6583 \triangleright

starting at 1,5 mm²: ⊲ VDE-REG 6584 ⊳

Conductor fine wire strands of tinned copper acc. to IEC 60228 resp. VDE 0295, Class 5

Insulation Thermoplastic elastomer (TPE)

Core identification code up to 5 cores coloured acc. VDE 0293-308 resp. HD 308 S2

more than 5 cores: black cores with white numbers

with GN/YE ground conductor acc. to DIN EN 50334 resp. VDE 0293-334

Inner sheath Thermoplastic elastomer (TPE)

Screen braid of tinned copper, coverage = 85% (nominal value)

Outer sheath polyurethane compound TMPU acc. to EN 50363-10-2 resp. VDE 0207-363-10-2

colour: yellow, similar RAL 1016

Electrical properties at 20°C

Rated voltage up to 1,0 mm²: 300 / 500 V

starting at 1,5 mm²: 450 / 750 V up to 1,0 mm²: 3000 V AC starting at 1,5 mm²: 3500 V AC

Mechanical and thermal properties

Minimum bending radius occasional flexing: 12,5 x cable diameter

fixed installation: 6 x cable diameter

Temperature range occasional flexing: -40 °C up to +90 °C max. conductor temperature

fixed installation: -50 °C up to +90 °C max. conductor temperature

Flammability flame retardant acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Halogen free acc. to VDE 0472-815

UV resistance acc. to EN 50618 resp. VDE 0283-618

acc. to EN 50620 resp. VDE 0285-620

acc. to EN ISO 4892-2-2013, method A (change of colour allowed)

Oil resistance acc. to EN 50363-10-2 resp. VDE 0207-363-10-2

MUD resistance acc. to IEC 61892-4 Annex D

 Water-resistance
 acc. to EN 50525-2-21 resp. VDE 0285-525-2-21

 Tests
 acc. to IEC 60811 resp. VDE 0473 and VDE 0472

General requirements These cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive)

Creator: LABU / PDC Document: DB0012752EN

Released: ALTE / PDC Version: 07

Page 1 of 1