

0162019	DATA SHEET	
Valid from: 01.04.2019	IEC compensating cable KN 13 L-SIL 2x1,5 oval	

Application

The compensating cable KN 13 L-SIL 2 x 1,5 mm² is a silicone and glass fibre insulated cable which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for fixed installation in dry rooms. It may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range.

Design

Conductor	1.5 mm ² (48 x 0.20 mm)	
Conductor material	KCA alloying, accuracy class 2 according IEC 60584	
	Positive conductor:	Fe (iron)
	Negative conductor:	CuNi (cupronickel)
Core insulation	Silicone compound	
Core identification	Positive conductor:	green
	Negative conductor:	white
Core layering	Cores parallel next to each other	
Outer sheath	Glass fibre braiding with interweaved, green identification thread	

Electrical properties

Limiting deviation class 2	±100 µV (±2.5 °C) / measuring point temperature +900 °C
----------------------------	---------------------------------------------------------

Mechanical and thermal properties

Temperature range	occasional flexing:	-25 °C up to +180 °C
Minimum bending radius	occasional flexing:	12 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2	

Creator: TOME/PCM Released: ALTE/PDC	Document: DB0162019EN Version: 02	Page 1 of 1
-----------------------------------------	--------------------------------------	-------------